
OSRAM ECOPACK-T5 DALI

Batten luminaires for 16 mm fluorescent lamps



Product benefits


- Long lamp life thanks to cut-off technology
- Energy-efficient

Product features

- Batten luminaires without a cover and lamp for fixed connections
- Luminaire color: white (RAL 9016)



Product family datasheet



Product line drawing

Product family datasheet

Technical data

Product description	Electrical data				Photometrical data	Light technical data	Dimensions & weight	
	Operating mode	Lamp wattage	Nominal voltage	Mains frequency	Luminaire efficiency	Light distribution	Length	Width
ECOPACK-T5 DALI 14/24 W	ECG Multiwatt Dimmable DALI	14/24 W	220...240 V	50...60 Hz	0.84	Symmetric	584.0 mm	38.0 mm
ECOPACK-T5 DALI 21/39 W	ECG Multiwatt Dimmable DALI	21/39 W	220...240 V	50...60 Hz	0.84	Symmetric	884.0 mm	38.0 mm
ECOPACK-T5 DALI 28/54 W	ECG Multiwatt Dimmable DALI	28/54 W	220...240 V	50...60 Hz	0.84	Symmetric	1184 mm	38.0 mm
ECOPACK-T5 DALI 35/49/80 W	ECG Multiwatt Dimmable DALI	35/49/80 W	220...240 V	50...60 Hz	0.84	Symmetric	1484 mm	38.0 mm

Product description				Colors & materials	Additional product data		Capabilities
	Height	Mounting hole spacing, length	Cable penetration	Body material	Number of lighting outlets	Equipped with lamp	Type of installation
ECOPACK-T5 DALI 14/24 W	58.0 mm	538.0 mm	105.0 mm	Steel	1	No	Surface-mounted
ECOPACK-T5 DALI 21/39 W	58.0 mm	838.0 mm	478.0 mm	Steel	1	No	Surface-mounted
ECOPACK-T5 DALI 28/54 W	58.0 mm	1138.0 mm	592.0 mm	Steel	1	No	Surface-mounted
ECOPACK-T5 DALI 35/49/80 W	58.0 mm	1438.0 mm	742.0 mm	Steel	1	No	Surface-mounted

Product description	Dimmable	Type of connection	Holder designation	Accessories	Certificates & standards	
					Glow Wire Test according to IEC 695-2-1	Type of lamp compatible w. luminaires
ECOPACK-T5 DALI 14/24 W	Yes	Terminal, 5-pole	G5	Pendant kit (4050300792200)	960 °C	FDH-14+24/XX/1B-L/P-G5-16/549
ECOPACK-T5 DALI 21/39 W	Yes	Terminal, 5-pole	G5	Pendant kit (4050300792200)	960 °C	FDH-21+39/XX/1B-L/P-G5-16/849
ECOPACK-T5 DALI 28/54 W	Yes	Terminal, 5-pole	G5	Pendant kit (4050300792200)	960 °C	FDH-28+54/XX/1B-L/P-G5-16/1149

Product family datasheet

Product description	Dimmable	Type of connection	Holder designation	Accessories	Certificates & standards	
					Glow Wire Test according to IEC 695-2-1	Type of lamp compatible w. luminaires
ECOPACK-T5 DALI 35/49/80 W	Yes	Terminal, 5-pole	G5	Pendant kit (4050300792200)	960 °C	FDH-35+80-L/P-G5-16/1449

Product description	EEL of control gear in luminaire	Protection class	Type of protection	Protection against ignition and fire	Protection class IK (shock resistance)	Country specific categorizations
						Order reference
ECOPACK-T5 DALI 14/24 W	A1 BAT	I	IP20	F,MM	IK07	72621-99
ECOPACK-T5 DALI 21/39 W	A1 BAT	I	IP20	F,MM	IK07	72622-99
ECOPACK-T5 DALI 28/54 W	A1 BAT	I	IP20	F,MM	IK07	72623-99
ECOPACK-T5 DALI 35/49/80 W	A1 BAT	I	IP20	F,MM	IK07	72624-99

Product family datasheet

Equipment / Accessories

- With QUICKTRONIC QT_i DALI electronic control gear
 - Suitable for both T5 HE and T5 HO lamps
-

Application advice

For more detailed application information and graphics please see product datasheet.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.