

EK EKPE 180 T



Sample photo

Order symbol: EKPE 180 T
Product nbr: 2538146
Description: Enclosure, PC
Remarks: Transparent cover

EAN: 6418074013866
EI. number:
 Finland: 3425472
 Electric No. Italy: 7502145
 Electric No. Sweden: 2538146

Including: Flanged Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:	
mm:	380	280	180	EKPG	Base, PC
inch:	15.0	11.0	7.1	EKP 30-G	Cover
				EKP 80-G	Cover

Materials:		Accessories:	
Material:	Polycarbonate	EKP 30-T	Cover
Base colour:	RAL 7035 -light grey	EKP 80-T	Cover
Cover screws material:	Polyamide	EKPVT	Mounting plate
Cover colour:	Clear transparent	EKPXT	Mounting plate isolated
Cover screws colour:	Grey	EKV 22	DIN-35 Mounting rail
Gasket material:	Polyurethane	EKV 32	DIN-35 Mounting rail
		EKPZR	Extension frame

Temperatures:		Rating:	
Temperature °C (short term):	-40 ... 120 °C	Ingress Protection (EN 60529): IP66/IP67	
Temperature °C (continuous):	-40 ... 80 °C	Impact Resistance (EN 62262): IK08	
Temperature °F (short term):	-40 ... 250 °F	Electrical insulation: Totally insulated	
Temperature °F (continuous):	-40 ... 175 °F	Halogen free (DIN/VDE 0472, Part 815): 1	
		UV resistance: UL 508	
		Flammability Rating: UL 746C 5"	
		Glow Wire Test (IEC 695-2-1) °C: 960	
		NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12	

Accessories:		Certificates:	
EKPE	Base, PC	Germanischer Lloyd (GL)	
		SGS Fimko	
		Lloyds Register of Shipping (LR)	
		Gost R	

