

**EK EKPK 230 G**



Sample photo

**Order symbol:** EKPK 230 G  
**Product nbr:** 2538058  
**Description:** Enclosure, PC  
**Remarks:** Grey cover

**EAN:** 6418074013637  
**EI. number:**  
 Finland: 3425428  
 Electric No. Italy: 7501155  
 Electric No. Sweden: 2538058

Including: Flanged Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:	
mm:	380	280	230	EKPL	Base, PC
inch:	15.0	11.0	9.1	EKP 30-G	Cover
				EKP 80-G	Cover

Materials:	
<b>Material:</b>	Polycarbonate
<b>Base colour:</b>	RAL 7035 -light grey
<b>Cover screws material:</b>	Polyamide
<b>Cover colour:</b>	RAL 7035 -light grey
<b>Cover screws colour:</b>	Grey
<b>Gasket material:</b>	Polyurethane

EKP 30-T	Cover
EKP 80-T	Cover
EKPVT	Mounting plate
EKPXT	Mounting plate isolated
EKV 22	DIN-35 Mounting rail
EKV 32	DIN-35 Mounting rail
EKPZR	Extension frame

Temperatures:	
<b>Temperature °C (short term):</b>	-40 ... 120 °C
<b>Temperature °C (continuous):</b>	-40 ... 80 °C
<b>Temperature °F (short term):</b>	-40 ... 250 °F
<b>Temperature °F (continuous):</b>	-40 ... 175 °F

Rating:	
Ingress Protection (EN 60529):	IP66/IP67
Impact Resistance (EN 62262):	IK08
Electrical insulation:	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	1
UV resistance:	UL 508
Flammability Rating:	UL 746C 5"
Glow Wire Test (IEC 695-2-1) °C:	960
NEMA Class:	NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12

Accessories:	
EKPK	Base, PC

Certificates:	
Germanischer Lloyd (GL)	
SGS Fimko	
Lloyds Register of Shipping (LR)	

Gost R

