

KERN EOB 15K5

KERN

Allround parcel scale with robust stainless steel weighing plate



Category

Brand	KERN
Product category	Industrial scales
Product group	Platform scales

Measuring System

Readability [d]	5 g
Weighing capacity [Max]	15 kg
Eccentric loading at 1/3 [Max]	0,015 kg
Reproducibility	0,005 kg
Linearity	± 0,01 kg
Weighing system	Strain gauge
Resolution	3.000
Tare range	15 kg
Units	kg lb PCS
Default unit	kg
Stabilization time	3 s
Warm-up time	10 min
Adjustment options	Adjusting with external weight
Recommended adjusting weight	10 kg (M2)
Possible calibration points	10 kg

Approval

CE mark	✓
---------	---

Display

Display digit height	25 mm
Display backlight	✓

Construction

Dimension display device (W×D×H)	235×114×51 mm
----------------------------------	---------------

Dimensions weighing platform (W×D×H)	315×305×57 mm
Material housing	plastic
Material display housing	Plastics
Material weighing plate	stainless steel
Wall mount	✓
Display device cable length	1,8 m

Functions

Number of keys for operation	4
Auto-off interval(s) in battery mode/rechargeable battery mode	off 1 min - 99 min
Tare function	manual (multi)
Hold function	✓
Function for averaging under unstable weighing conditions	✓
Underfloor weighing	None
IP protection - complete device	-
IP protection - display	no IP protection
IP protection - load cell	no IP protection
IP protection - platform	no IP protection

Power Supply

Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	9 V, 100 mA
Plug-in power supply type	Power adapter
Supplied plug-in power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO AUS UK US CH
Plug-in power supply / adapter for countries - optional	EURO UK US CH
Battery	4×1.5 V AA
Battery operating time	60 h

Environmental conditions

Humidity of environment [Max]	80 %
Ambient temperature [Min]	5 °C
Ambient temperature [Max]	35 °C

Packing & Shipping

Readability force [d] (N)	1 d
Shipping method	Parcel service
Dimensions packaging (W×D×H)	370×360×140 mm
Net weight approx.	3,8 kg
Gross weight approx.	5,0 kg

KERN EOB 15K5



Allround parcel scale with robust stainless steel weighing plate

Services (optional)

Article number for adjustment at the location of installation	961-248
Article number for DAkkS calibration	963-128
Article number for certificate of conformity (verification)	969-517

Piktogramme

STANDARD



OPTION

