

Product datasheet

Specifications



APC Easy Rack PDU, Basic, 0U, 1 Phase, 7.4kW, 230V, 32A, 21 x SCHUKO outlets, IEC60309 2P + E inlet

EPDU1132B-SCH

Overview

Lead time Usually in Stock

Main

Main Input Voltage	200 V 208 V 230 V
PDU type	Basic
Main Output Voltage	230 V
Input Connection Type	IEC 60309 32 A 2P + E
Number of rack unit	0U
Cable length	3.00 m
Number of cables	1
Provided equipment	Installation guide Toolless mounting kit Vertical mounting brackets

Physical

Colour	Black
Height	150.6 cm
Width	6.2 cm
Depth	4.44 cm
Net weight	4.3 kg
Mounting location	Side
Mounting preference	No preference
Mounting mode	Rack-mounted
Mounting position	Vertical

Input

Input current limits	32 A
Load capacity	7360 VA
Network frequency	50/60 Hz

Output

Number of power socket outlets 21Schuko CEE 7

Conformance

Product certifications CE
TÜV

Environmental

Ambient air temperature for operation -5...45 °C

Relative humidity 5...95 %

Operating altitude 0...10000 ft

Ambient air temperature for storage -25...65 °C

Storage Relative Humidity 5...95 %

Storage altitude 0.00...15240.00 m

Packing Units

Unit Type of Package 1 PCE

Number of Units in Package 1 1

Package 1 Height 166 cm

Package 1 Width 11 cm

Package 1 Length 16 cm

Package 1 Weight 5.5 kg

Offer Sustainability

REACH Regulation [REACH Declaration](#)

REACH free of SVHC Yes

EU RoHS Directive Compliant
[EU RoHS Declaration](#)

Mercury free Yes

RoHS exemption information [Yes](#)

WEEE The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty 1 year repair or replace

Recommended replacement(s)