

Product datasheet

Specifications



APC Easy Rack, 42U, Black, With Roof, Castors, Feet, 4 Brackets, and Side Panels, No Bottom, 1991H x 600W x 1000D mm

ER6202FP1

Overview

Lead time Usually in Stock

Main

Product or component type Rack enclosure

Number of rack unit 42U

Provided equipment
Baying hardware
Key(s)
Keyed-alike doors and side panels
Leveling feet
Mounting hardware
Pre-installed casters
Side panels

Physical

Height 199.1 cm

Width 60 cm

Depth 100 cm

Net weight 109 kg

Colour Black

Mounting mode Not rack-mountable

Maximum mounting depth 83.82 cm

Minimum mounting depth 19.05 cm

Rack width 19"

Marking
18 gauge front door
19 gauge rear door
16 gauge post
14 gauge EIA mounting rail

Permanent permissible load
1199.75 kg static
599.65 kg dynamic

Conformance

Standards
UL 2416
EIA-310E

Packing Units

Unit Type of Package 1 PCE

Number of Units in Package 1	1
Package 1 Height	44 cm
Package 1 Width	210 cm
Package 1 Length	97 cm
Package 1 Weight	120 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
RoHS exemption information	Yes

Contractual warranty

Warranty	5 years
----------	---------

Recommended replacement(s)