

Product datasheet

Specifications



APC Easy Rack, 42U, Black, With Roof, Castors, Feet, 4 Brackets, and Side Panels, No Bottom, 1991H x 600W x 1100D mm

ER6212

Overview

Lead time Usually in Stock

Main

Product or component type	Rack enclosure
Number of rack unit	42U
Provided equipment	Baying hardware Key(s) Keyed-alike doors and side panels Leveling feet Mounting hardware Pre-installed casters Side panels

Physical

Height	199.1 cm
Width	60 cm
Depth	110 cm
Net weight	105.2 kg
Colour	Black
Mounting mode	Not rack-mountable
Maximum mounting depth	93.98 cm
Minimum mounting depth	24.16 cm
Rack width	19"
Marking	18 gauge front door 19 gauge rear door 16 gauge post 14 gauge EIA mounting rail
Permanent permissible load	1199.75 kg static 599.65 kg

Conformance

Standards	UL 2416 - EIA-310E
-----------	--------------------------

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Number of Units in Package 1	1
Package 1 Height	212 cm
Package 1 Width	115 cm
Package 1 Length	65 cm
Package 1 Weight	112 kg
Pallet layers	1

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
RoHS exemption information	Yes

Contractual warranty

Warranty	2 Years repair or replaceNote- extended warranty options are available
-----------------	--

Recommended replacement(s)