

# Product data sheet

Specifications



## APC Easy Rack, 24U, Black, With Roof, Castors, Feet, 4 Brackets, and Side Panels, No Bottom, 1198H x 600W x 1000D mm

ER6402

### Overview

Lead time Usually in Stock

### Main

Product or component type Rack enclosure

Number of rack unit 24U

Provided equipment  
Baying hardware  
Key(s)  
Keyed-alike doors and side panels  
Leveling feet  
Mounting hardware  
Pre-installed casters  
Side panels

### Physical

Height 119.8 cm

Width 60 cm

Depth 100 cm

Net weight 71.4 kg

Colour Black

Mounting mode Not rack-mountable

Maximum mounting depth 83.82 cm

Minimum mounting depth 19.05 cm

Rack width 19"

Marking  
18 gauge front door  
19 gauge rear door  
16 gauge post  
14 gauge EIA mounting rail

Permanent permissible load  
1199.75 kg static  
599.65 kg dynamic

### Conformance

Standards  
UL 2416  
UL 60950-1  
EIA-310E

### Packing Units

Unit Type of Package 1 PCE

<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	133 cm
<b>Package 1 Width</b>	65 cm
<b>Package 1 Length</b>	105 cm
<b>Package 1 Weight</b>	77 kg

## Offer Sustainability

<b>REACH Regulation</b>	<a href="#">REACH Declaration</a>
<b>REACH free of SVHC</b>	Yes
<b>EU RoHS Directive</b>	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
<b>Mercury free</b>	Yes
<b>China RoHS Regulation</b>	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
<b>RoHS exemption information</b>	<a href="#">Yes</a>

## Contractual warranty

<b>Warranty</b>	5 year repair or replace
-----------------	--------------------------

## Recommended replacement(s)