


Product datasheet

Specifications



APC Easy Rack, 48U, Black, With Roof, Castors, Feet, 4 Brackets, and Bottom, No Side Panels, 2258H x 600W x 1000D mm

ER6800

Overview

Lead time Usually in Stock

Main

Product or component type Rack enclosure

Number of rack unit 48U

Provided equipment
Baying hardware
Key(s)
Doors
Leveling feet
Mounting hardware
Pre-installed casters

Physical

Height 225.8 cm

Width 60 cm

Depth 100 cm

Net weight 85.2 kg

Colour Black

Mounting mode Not rack-mountable

Maximum mounting depth 83.82 cm

Minimum mounting depth 24.16 cm

Rack width 19"

Marking
18 gauge front door
19 gauge rear door
16 gauge post
14 gauge EIA mounting rail

Permanent permissible load
1199.75 kg static
599.65 kg dynamic

Conformance

Standards
UL 2416
UL 60950-1
EIA-310E

Packing Units

Unit Type of Package 1 PCE

Number of Units in Package 1	1
Package 1 Height	239 cm
Package 1 Width	65 cm
Package 1 Length	105 cm
Package 1 Weight	92 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
RoHS exemption information	Yes

Contractual warranty

Warranty	5 year repair or replace
-----------------	--------------------------

Recommended replacement(s)