

Product datasheet

Specifications



APC Easy Rack, 48U, Black, With Roof, Castors, Feet, 4 Brackets, and Side Panels, No Bottom, 2258H x 600W x 1000D mm

ER6802

Overview

Lead time Usually in Stock

Main

Product or component type	Rack enclosure
Number of rack unit	48U
Provided equipment	Baying hardware Key(s) Keyed-alike doors and side panels Leveling feet Mounting hardware Pre-installed casters Side panels

Physical

Height	225.8 cm
Width	60 cm
Depth	100 cm
Net weight	113.2 kg
Colour	Black
Mounting mode	Not rack-mountable
Maximum mounting depth	83.82 cm
Minimum mounting depth	24.16 cm
Rack width	19"
Marking	18 gauge front door 19 gauge rear door 16 gauge post 14 gauge EIA mounting rail
Permanent permissible load	1199.75 kg static 599.65 kg dynamic

Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Number of Units in Package 1	1
Package 1 Height	239 mm
Package 1 Width	105 cm
Package 1 Length	65 cm
Package 1 Weight	120 kg
Pallet layers	1

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
RoHS exemption information	Yes

Contractual warranty

Warranty	5 year repair or replace
-----------------	--------------------------

Recommended replacement(s)