

# Product datasheet

Specifications



## APC Easy Rack, 48U, Black, With Roof, Castors, Feet, 4 Brackets, and Bottom, No Side Panels, 2258H x 800W x 1200D mm

ER8820

### Overview

Lead time Usually in Stock

### Main

Product or component type Rack enclosure

Number of rack unit 48U

Provided equipment  
Baying hardware  
Key(s)  
Doors  
Leveling feet  
Mounting hardware  
Pre-installed casters

### Physical

Height 225.8 cm

Width 80 cm

Depth 120 cm

Net weight 114 kg

Colour Black

Mounting mode Not rack-mountable

Maximum mounting depth 104.14 cm

Minimum mounting depth 24.16 cm

Rack width 19"

Marking  
18 gauge front door  
19 gauge rear door  
16 gauge post  
14 gauge EIA mounting rail

Permanent permissible load  
1199.75 kg static  
599.65 kg dynamic

### Conformance

Standards  
UL 2416  
UL 60950-1  
EIA-310E

### Packing Units

Unit Type of Package 1 PCE

<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	239 cm
<b>Package 1 Width</b>	85 cm
<b>Package 1 Length</b>	125 cm
<b>Package 1 Weight</b>	123 kg

## Offer Sustainability

<b>Sustainable offer status</b>	Green Premium product
<b>REACH Regulation</b>	<a href="#">REACH Declaration</a>
<b>REACH free of SVHC</b>	Yes
<b>EU RoHS Directive</b>	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
<b>Mercury free</b>	Yes
<b>China RoHS Regulation</b>	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
<b>RoHS exemption information</b>	<a href="#">Yes</a>

## Contractual warranty

<b>Warranty</b>	5 year repair or replace
-----------------	--------------------------

## Recommended replacement(s)