Manual tensioning tool plastic housing

EVO9 up to 13.5 mm strap width

The EVO9 is available in a standard grip span 90 mm (EVO9) or short grip span 80 mm (EVO9SP), for smaller hands. Both tools perform between 53 N and 307 N. The EVO9HT (high tension) was designed to apply HellermannTyton cable ties from 120 N until 516 N with a maximum width of 13.5 mm.

Features and benefits

- Standard grip span (90 mm) and short grip span (80 mm) available
- Ergonomic, slip-proof handle for a comfortable and secure grip
- Extremely low-maintenance
- Fast and precise application with minimum effort (TLC-technology)
- · Convenient and simple tension adjustment
- Integrated 3 position quick adjustment override (EVO9/EVO9SP/EVO9HT)
- · Housing made of resilient and lightweight glass fibre-reinforced polyester



The EVO9 with TLC technology.

EVO9SG for the application of Soft Grip ties!

ТҮРЕ	Strap Width max.	Strap Thickness max.	Weight	Article-No.
EVO9SG	12.7	2.9	0.357 kg	110-80130
EVO9	13.5	2.0	0.357 kg	110-80002
EVO9SP	13.5	2.0	0.361 kg	110-80003
EVO9HT	13.5	2.0	0.357 kg	110-80017
SP EVO9 Blade	-	-	0.002 kg	110-80037

All dimensions in mm. Subject to technical changes.

