



→ See All Eaton 5SC UPS Documentation

→ See all Eaton 5SC models

5SC3000IRT

Eaton 5SC 3000 VA Rack/Tower

General	
Topology	Line-interactive high frequency with booster + fader, pure sinewave output
Configuration	Rack/Tower
Part Number	5SC3000IRT
Color	Black
Rating (VA/Watts)	3000/2700
Dimensions (H x W x D, mm)	86.2 x 441 x 647
Weight (kg)	35.3
Warranty	2 years

Electrical Input

Connection (1) IEC-320-C20



Input Voltage Range 184V-276V Nominal Voltage 230V

Input frequency Range Without Using 45–55Hz (50Hz system), 55–65Hz (60Hz system)

Electrical Output

Voltages 230V (+6/-10 %) (Adjustable to 220V/230V/240V)

Outlets (8) IEC-320-C13 (1) IEC-320-C19






Output Frequency 50/60Hz +/-0.1 % (autosensing)

Battery

80

110 Standard Runtime

Mouseover graph for detailed runtime values



Battery Management ABM®, Automatic battery test, deep discharge protection

Communications	
Communication Ports	1 USB port + 1 RS232 serial port and relay contacts (USB and RS232 ports cannot be used simultaneously) + 1 mini terminal block for remote ON/OFF and Remote Power Off
Communication Slot	1 slot for Network management card or Relay card

Environmental & Standards	
Audible Noise	<45 dB
Operating Temperature	0 to 40°C
Safety markings	IEC/EN 62040-1, UL 1778
EMC Markings	IEC/EN 62040-2
Approvals	CE, CB report (TUV)

In the interests of continuous product improvement, all specifications are subject to change without notice.

Privacy Policy
Terms & Conditions
Copyright

© 2017 Eaton All Rights Reserved