

EloPOS™ Pack

Windows Compute Engine for Point-of-Sale Applications





Connectivity-Rich



Compact Form-Factor



Product Overview

i3 & i5 Models Offer: TPM 2.0, Intel AMT,
Intel Standard Manageability & Intel vPro

The EloPOS Pack delivers a powerful enterprise-ready compute platform in a sleek, compact form factor. Backed by the security and infrastructure of a Windows-based system and the speed of the Intel Q370 Chipset, the EloPOS Pack provides the power you need to run your business. With versatile connectivity options, plug in anything from Elo's latest monitor via single cable USB-C to a legacy printer requiring a 12V powered-USB. The system provides flexibility to make upgrades as your business requirements change.

Whether you want Windows 10 or a no-OS model to run Linux, the enterprise-ready EloPOS Pack provides the freedom to adapt to your infrastructure. To get you up and running quicker, the no-OS models have been pretested with Linux SuSE, Ubuntu and Red Hat operating systems.

Well suited for Self-Service, Point-of-Sale and Industrial Automation applications

Secure Mounting - Easily secure the EloPOS Pack to any counter in a snap. For added security, you can use the Kensington locks.

EloPOS Pack

	Intel® Celeron® Processor G4900T	Intel Core i3-9100TE Processor (6M Cache, up	Intel Core i5-9500TE Processor (9M Smart		
Processor	(2M Cache, up to 2.9 GHz)	to 3.20 GHz)	Cache, up to 3.60 GHz by Intel Turbo Boost Technology 2.0) Intel vPro Support		
Chipset	Intel Q370 Express				
Video	Intel UHD Graphics 610 Intel UHD Graphics 630				
BIOS	AMI				
Storage	128GB M.2 SATA SSD, 72 TBW (GB equals one billion bytes when referring to storage capacity. Accessible capacity may be less.)				
Memory	4GB 2400MHz DDR4 SO-DIMM on 1 of 4 slots	8GB 2400MHz DDR4 SO-DIMM on 1 of 4 slots	8GB 2666MHz DDR4 SO-DIMM on 1 of 4 slots		
	(Expandable to 64GB maximum on 4 slots)	(Expandable to 64GB maximum on 4 slots)	(Expandable to 64GB maximum on 4 slots)		
	Maximum memory using 4 slots. Expandable up to 64GB maximum, SO-DIMM DDR4-2133. Check brand of the memory included in your unit before purchasing the memory kit.				
Operating Systems Supported	No Operating System Microsoft Windows 10 IoT Enterprise LTSC 64-bit				
Languages	Windows 10 - 36 Language groups				
Control Buttons	Power				
I/O Ports	1 x HDMI port, 1 x LAN RJ45 (Gigabit), 1 x 24V and 5 x 12V powered USB, 1 x RJ50, 12V/24V Cash Drawer Port on I/O (EPSON Pinout, 24V default; selectable by internal swtich), 1 x Full-function USB-C (Power up to 27W, USB 3.0, Display Port), 1 x 3.5 mm headset jack				
Wireless	802.11 a/b/g/n/ac 2.4GHz and 5GHz				
Antenna	2T2R design with External SMA connector				
Bluetooth	Bluetooth 5.0				
TPM	TPM 2.0				
AMT	Active Management Technology (Intel AMT 11.0) Support.				
Real Time Clock	Replaceable CR2032 lithium metal battery for clock				
Power Supply	External 24VDC universal-type power supply brick	k, AC input voltage: 100-240 VAC, Input frequency: 50-	60 Hz, Maximum output power: 180W		
Power Consumption	32.415W	48.87W	55.34W		
Mounting Options	Bracket mounts to table with screws, System slides forward to engage hooks on bracket				
Other Features	Serviceable internal components. Kensington Mano Security Slot. Kensington lock slot (Standard Size).				
Upgrade Options	256GB M.2 SATA SSD - Elo P/N: E206556, E762128, E503575; 512GB M.2 SATA SSD - Elo P/N: E865041; 4GB DDR4 Memory SO-DIMM - Elo P/N: E27541: E951667, E952623; 8GB DDR4 Memory SO-DIMM - Elo P/N: E275635, E951857, E952813				
Dimensions	10.9" x 1.4" x 9.4" / 276 mm x 37 mm x 237.5 mm				
Shipping Box Dimensions	16.3" x 6.7" x 13.6" / 414 mm x 169 mm x 346 mm				
Weight	Unpackaged: 5.76 lbs / 2.6 kg; Packaged: 11.02 lbs / 5.0 kg				
Temperature	Operating: 0°C to 40°C (32°F to 104°F); Storage: -20°C to 60°C (-4°F to 140°F)				
Humidity (non-condensing)	Operating: 10% to 90%; Storage: 0% to 95% (38.7°C max wet bulb temperature)				
Agency Approvals	UL/cUL, FCC, TUV, CE, CB, Mexico NOM, C-Tick/RCM, VCCI, Argentina S-Mark, CCC				
Compliance	Energy Star 7.1				
Warranty	3 years				
Extended Warranty	4 year coverage - Elo P/N: E819598 ; 5 year coverage - Elo P/N: E819795 3 year coverage + AUR - Elo P/N: E820186; 4 year coverage + AUR - Elo P/N: E820388; 5 year coverage + AUR - Elo P/N: E820582				
MTBF	50,000 hours demonstrated				
What's in the box	EloPOS Pack, North America Power Cord (1800+/-50mm), (6 ft +/- 1 inch), EU Power Cord (1800+/-50mm), Power Adapter – 180W, Cable RJ-50 to DB-9 (900+/-30mm), (3 ft +/- 1 inch), USB Type-C cable (1800+/-50mm), (6 ft +/- 1 inch), HDMI cable (1800+/-50mm), (6 ft +/- 1 inch), 2x SMA Antenna, Quick Installation Guide (QIG)				

Ordering Information

Part Numbers	OS	Processor	Storage	Memory (RAM)
E924330	Windows 10	G4900T	128GB SSD	4GB RAM
E924535	Windows 10	i3-9100TE	128GB SSD	8GB RAM
E924731	Windows 10	i5-9500TE	128GB SSD	8GB RAM
E982296	No OS	G4900T	128GB SSD	4GB RAM
E117640	No OS	G4900T	128GB SSD	8GB RAM
E982670	No OS	i3-9100TE	128GB SSD	8GB RAM
E582680	No OS	i3-9100TE	128GB SSD	16GB RAM
E982479	No OS	i5-9500TE	128GB SSD	8GB RAM
E780801	No OS	i5-9500TE	512GB SSD	8GB RAM
E582494	No OS	i5-9500TE	128GB SSD	16GB RAM

Learn more about Elo at **EloTouch.com**.

Americas Europe (EMEA) Asia Pacific

Tel +1 408 597 8000 Tel +32 16 930 136 Tel +86 (21) 3329 1385 elosales.na@elotouch.com EMEA.Sales@elotouch.com www.elotouch.com.cn



