
Epson TM-U295 (292): Serial, w/o PS, EDG

DATASHEET



SLIP IMPACT PACKAGED PRINTER; Serial; Epson Dark Grey (EDG); no Power Supply

KEY FEATURES

PRODUCT SPECIFICATIONS

FONTS & STYLES	
Column capacity	35 cps / 42 cps
PAPER	
Paper size	80 - 182 mm (W) x 69 - 257 mm (H)
Copy capability	two copies plus one original
INTERFACES	
Interfaces	RS-232, Drawer kick-out
POWER	
Power Supply	PS-180 (option)
GENERAL	
Product dimensions	180 x 191 x 102 mm (Width x Depth x Height)
Product weight	1.6 kg
Color	Epson Dark Gray
Noise Level	Operation: 65 dB (A)
FONTS & STYLES	
Print Speed	1.90 ~ 2.30 Ips
Column capacity slip	35 cps / 42 cps
Character size	1.6 mm (W) x 2.9 mm (H) / 1.3 mm (W) x 2.9 mm (H)
Character set	95 Alphanumeric, 32 International, 128 x 4 Graphic
Characters per inch	13.5 cpi / 16.2 cpi
DATA BUFFER	
Data Buffer	512 Bytes or 35 Bytes
OTHER	
Warranty	12 months Carry in Optional warranty extension available

LOGISTICS INFORMATION

SKU	C31C163292
EAN code	8715946319681
Dimensions Single Carton	235 x 279 x 190 mm
Carton Weight	1.9 Kg
Multiple Order Quantity	4 Units
Country of Origin	Portugal
Pallet Size Euro	96 Units (24 x 5)
Pallet Size Block	128 Units (32 x 5)

Epson TM-U295 (292): Serial, w/o PS, EDG

WHAT'S IN THE BOX

- Main unit
- User manual
- Ribbon

SUPPLIES

- Epson ERC27B Ribbon Cartridge for TM-U290/II, - U295, M-290, black
C43S015366

OPTIONAL ACCESSORIES

- Epson PS-180
C32C825341
- Epson AC Cable
2020111
- Epson AC Cable, UK cable
2093752
- Epson AC Cable, EURO cable
2119140



For more information please contact:

Telephone: 01952 607111 (UK)+
01 436 7742 (Republic of Ireland)
E-mail: enquiries@epson.co.uk
Chat: etalk.epson-europe.com
Fax: 0871 222 6740
+ Local call rate.

Web: www.epson.co.uk
www.epson.ie

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners.
Product information is subject to change without prior notice.

EPSON[®]