Epson TM-T88V (082): Serial, PS, EDG, UK



The TM-T88V is a true breakthrough in the development of POS receipt printers, and the results are better for your budget and the environment. This is most clearly demonstrated with the paper reduction function. which cuts down on waste and cost. Green credentials are further proved by this being the first thermal receipt printer to be Energy Star qualified.

Actual print speed is an impressive and efficient 300mm per second while multiple grey scale printing enables better representation of logos and graphic images. The TM-T88V works on several platforms, so it's simple to integrate into your network and it also comes with in-built USB IF which means easy migration to USB in the future.

This is a highly reliable and easy-to-use POS printer, but with the interest of the customer being paramount, we have included a 4-year warranty as standard.

This product meets the strict ENERGY STAR® guidelines set by the European Commission. Epson is a global manufacturer committed to protecting the environment for future generations by offering a range of ENERGY STAR® products. This is achieved by significantly reducing electricity usage, which saves energy, money and the environment, without compromising quality.

DATASHEET











KEY FEATURES

- High-speed printing of up to 300 mm/sec. Same speed for internal graphics
- Multi greyscale printing for high quality logo printing
- Automatic paper reduction function saves money
- Outstanding reliability 4 years warranty included



PRODUCT SPECIFICATIONS

INTERFACES

Interfaces USB 2.0 Type B, RS-232, Drawer kick-out

POWER

Power Supply PS-180 & UK AC cable
Power Consumption standby: 0.1 A, Mean: 1.8 A

Operatingvoltage 24 V

GENERAL

Product dimensions 145 x 195 x 148 mm (Width x Depth x Height)

Product weight 1.6 kg
Color Epson Dark Gray
Noise Level Operation: 55 dB (A)

Installation horizontally, vertically, wall hanging

Interface connectors D.K.D. function (2 drivers)

Humidity Operation 10% - 90%, Storage 10% - 90%

FONTS & STYLES

Print Speed 300 mm/sec

Character size 0.99 mm (W) x 2.4 mm (H) / 1.41 mm (W) x 3.39 mm (H)
Character set 95 Alphanumeric, 16 set International, 128 x 43 Graphic

Characters per inch 20 cpi / 15 cpi
Dot density 180 dpi x 180 dpi

OTHER

Warranty 48 months Carry in

LOGISTICS INFORMATION

SKU	C31CA85082	
EAN code	8715946466644	
Dimensions Single Carton	193 x 242 x 236 mm	
Carton Weight	2.5 Kg	
Multiple Order Quantity	4 Units	
Country of Origin	China	
Pallet Size Euro	128 Units (16 x 8)	
Pallet Size Block	192 Units (24 x 8)	

Epson TM-T88V (082): Serial, PS, EDG, UK

WHAT'S IN THE BOX

- PS-180 & AC cable
- Main unit
- User manual
- Thermal roll paper
- Power switch cover
- Connector Cover
- 58-mm width paper guide plate

OPTIONAL ACCESSORIES

- Epson PS-180 C32C825341
- Epson UB-E02 C32C824151
- Epson UB-P02II C32C823891
- Epson UB-R03 C32C824461
- Epson UB-S01
 C32C823361
- Epson UB-S09 C32C823861
- Epson UB-U01III C32C824111
- Epson UB-U02III C32C824121
- Epson UB-U03II C32C824131



For more information please contact:

Telephone: 01952 607111 (UK)+ 01 436 7742 (Republic of Ireland) E-mail: enquiries@epson.co.uk Chat: etalk.epson-europe.com Fax: 0871 222 6740 + Local call rate. Web: www.epson.co.uk www.epson.ie

