

ColorWorks C3500 (012CD) (incl. NiceLabel CD)

DATASHEET



Whether you're printing labels, tickets or tags, the ColorWorks C3500 (TM-C3500) is designed to help your business print a wide variety of colourful labels in-house. Featuring high-quality print speeds of up to 103mm/sec and individual pigment ink cartridges, your business can save money on outsourcing label production, by printing labels on-demand.

Print your own labels

With the ColorWorks C3500 (TM-C3500), you can easily customise and print your own colour labels. Whether it's printing packaging labels with colourful logos and pictures or tickets and ID cards with important barcodes and product information, this printer ensures you can print it all from one machine. It also helps you conform with GHS international chemical labelling guidelines, as labels can be printed on-demand without using pre-printed templates.

High-quality and durable

Thanks to the individual pigment ink cartridges, you can create fast-drying, highly detailed labels that are smudge, water and fade resistant. Not only will your labels look great, but the pigment ink's long-lasting, durable qualities make it perfect for a wide variety of environments.



KEY FEATURES

- **Durable prints**
Long-lasting pigment ink
- **Fast print speeds**
Print labels at up to 103mm/sec
- **Matte, glossy and more**
Print on a wide variety of media
- **Easy operation**
LCD screen for ink and printer status
- **Cost saving**
Individual ink cartridges

PRODUCT SPECIFICATIONS

TECHNOLOGY	
Printing Method	Epson Micro Piezo™ Serial inkjet printer
Nozzle Configuration	360 Nozzles per colour
Colours	Black, Cyan, Yellow, Magenta
Ink Technology	DURABrite™ Ultra
Category	Desktop colour label printer

PRINT	
Printing Speed	Max. 103 mm/sec at 360 x 360 dpi (printing width 56 mm)
Printing Resolution	Max. 720 x 360 dpi
Printing Width	max. 104 mm

SUPPORTED MEDIA	
Formats	Roll (4" external diameter), Fanfold media
Width	Min 30 mm, Max 112 mm
Type	Continuous label, Continuous paper, Die-cut label, Black mark paper, Black mark label

GENERAL	
Interfaces	USB 2.0 Type B, Ethernet interface (100 Base-TX / 10 Base-T)
Autocutter	Yes included
Power Supply	External
Supply voltage	100 ~ 240 V, 50 ~ 60 Hz
Power consumption	Printing: Appx. 30 W, standby: Appx. 3 W
Reliability	MTBF: 88,000 Hours, MCBF: 9,800,000 passes
Temperature / humidity	Printing: 10~35 °C (20~80 % RH), Storage: -20~60 °C (5~85 % RH)
Product dimensions	310 x 283 x 261 mm (Width x Depth x Height)
Product weight	12 kg

OTHER	
Warranty	12 months Carry in Optional warranty extension available

LOGISTICS INFORMATION

SKU	C31CD54012CD
EAN code	8715946539324
Dimensions Single Carton	440 x 400 x 425 mm
Carton Weight	15.04 Kg
Multiple Order Quantity	1 Units
Country of Origin	China
Pallet Size Euro	16 Units (4 x 4)
Pallet Size Block	24 Units (6 x 4)

ColorWorks C3500 (012CD) (incl. NiceLabel CD)

WHAT'S IN THE BOX

- AC Adaptor
- Driver and utilities (CD)
- Individual Ink Cartridges
- Main unit
- Maintenance box
- Roll paper
- User manual
- USB cable

SUPPLIES

- SJIC22P(C): Ink cartridge for ColorWorks C3500 (Cyan)
C33S020602
- SJIC22P(K): Ink cartridge for ColorWorks C3500 (Black)
C33S020601
- SJIC22P(M): Ink cartridge for ColorWorks C3500 (Magenta)
C33S020603
- SJIC22P(Y): Ink cartridge for ColorWorks C3500 (yellow)
C33S020604
- SJMB3500: Maintenance box for ColorWorks C3500 series
C33S020580
- Premium Matte Label - Continuous Roll: 51mm x 35m
C33S045417
- Premium Matte Label - Continuous Roll: 76mm x 35m
C33S045418
- Premium Matte Label - Continuous Roll: 102mm x 35m
C33S045419
- Matte Label - Continuous Roll: 76mm x 43m
1516052
- Matte Label - Continuous Roll: 105mm x 43m
1516054
- Premium Matte Ticket - Roll: 80mm x 50m
C33S045389
- Premium Matte Ticket - Roll: 102mm x 50m
C33S045390
- Premium Matte Label - Coil: 220mm x 750m
C33S045528
- PE Matte Label - Coil: 220mm x 750m
C33S045530
- Premium Matte Label - Die-cut Roll: 102mm x 51mm, 650 labels
C33S045531
- Premium Matte Label - Die-cut Roll: 102mm x 76mm, 440 labels
C33S045532



Better Products
for a Better Future
<http://eco.epson.com>



For more information please contact:

Telephone: 01952 607111 (UK)+
01 436 7742 (Republic of Ireland)
E-mail: enquiries@epson.co.uk
Chat: etalk.epson-europe.com
Fax: 0871 222 6740
+ Local call rate.

Web: www.epson.co.uk
www.epson.ie

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners.
Product information is subject to change without prior notice.

EPSON®