

# Epson TM-J7700(321) W/O MICR, WHITE, INC PSU, EU



Multifunctional POS inkjet printer offering fast, high quality receipt printing with a low total cost of ownership.

Designed to offer maximum performance and minimum running costs in retail environments, the TM-J7700 multifunctional POS printer uses inkjet technology to print receipts as well as slips, forms and coupons, with sharp, durable results.

#### **Faster, better inkjet technology**

Inkjet technology means that not only are printouts more detailed (600dpi compared to 180dpi for existing models), they're around twice as fast too, with a print speed of 100mm/s (23.2lps) compared to 43mm/s (13.5lps) for previous models.

#### **Low TCO**

Epson has managed to incorporate inkjet technology into this new model while retaining a similar low total cost of ownership to previous dot matrix printers.

#### **Simple maintenance**

The ink cartridges have an easy-install design ideal for busy retail counters, as well as drop-in paper roll for quick loading, and the ink formulation used offers better water and light resistance than dot matrix, so receipts and documents will last longer.

#### **Backwards compatible**

To make upgrading from existing models incredibly easy, the TM-J7700 is fully backwards-compatible with the TM-J7500 and has exactly the same footprint, so it can simply be swapped in. However, to integrate smoothly with the latest ePOS systems, the model offers both USB and Ethernet connection options.

#### **KEY FEATURES**

- **Versatile inkjet POS printer**  
Faster, better quality and more versatile
- **Low TCO**  
Similar overall costs to previous dot matrix model
- **Durable prints**  
Print is now more resistant to water and light
- **Simple maintenance**  
Ink and paper rolls are very easy to replace
- **Backwards compatible**  
Crisp, clear text and glossy photos

## PRODUCT SPECIFICATIONS

	<b>RECEIPT</b>	<b>SLIP / E/P</b>
Print speed	98 mm/sec	85 mm/sec
<b>FONTS &amp; STYLES</b>		
Character set	95 Alphanumeric	
<b>PAPER</b>		
Paper size	68 - 230 mm (W) x 68 - 297 mm (H), Min 68 - 152 mm	
<b>FONTS &amp; STYLES</b>		
Print Speed receipt	98 mm/sec	
Print Speed	98 mm/sec	
Print Speed (default)	98 mm/sec	
Print Speed graphic	98 mm/sec	
Print Speed slip	85 mm/sec	
Printing Font	ANK	
Printing Font Receipt	ANK	
Printing Font Slip	ANK	
Character set	95 Alphanumeric	
Character set slip	95 Alphanumeric	
Printing Characters	Text (incl. Euro symbol), Graphics, Barcode	
<b>INTERFACES</b>		
Interfaces	USB 2.0 Type B, Ethernet interface (100 Base-TX / 10 Base-T), Drawer kick-out, Customer Display	
<b>POWER</b>		
Power Supply	PS-180	
<b>GENERAL</b>		
Product dimensions	251 x 260 x 188 mm (Width x Depth x Height)	
Product weight	5.8 kg	
Colour	Black (EBCK)	
Noise Level	Operation (Roll): 55 dB (A)	
<b>OTHER</b>		
Warranty	12 months Carry in Optional warranty extension available	

## LOGISTICS INFORMATION

SKU	C31CF70321
EAN code	8715946639079
Country of Origin	China

Epson TM-J7700(321) W/O  
MICR,WHITE, INC PSU, EU

## WHAT'S IN THE BOX

- User manual (CD)
- Ink Cartridge
- USB cable
- Roll paper
- Power switch cover
- Power cable
- PS-180
- CD Manual
- Setup guide

## SUPPLIES

- SJIC33P(K) Ink Cartridge (C33S020655)

\* Warranty offers are not available for all countries. Please contact your local Epson representative.

For further information please contact your local Epson office or visit [www.epson-europe.com](http://www.epson-europe.com)

Austria 01 253 49 78 333 Belgium +32 (0)2 792 04 47 Czech 800/142 052 Denmark 44 50 85 85 Finland 0201 552 091 France 09 74 75 04 04

(Cost of local call, operator charges may apply) Germany +49 (0) 2159/92 79 500 Greece +30 211 198 62 12 Hungary 06800 147 83 Ireland 01 436 7742

Italy 02-660321 10 (0,12 /min) Luxembourg +352 27860692 Middle East +9714 8872172 Netherlands +31 (0)20 708 5099 Norway +47 67 11 37 00

Poland 0-0-800 4911299 (0,16 zł/min) Portugal 707 222 111 Russia (095) 777-03-55 Slovakia 0850 111 429 South Africa (+2711) 465-9621

Spain 93 582 15 00 Sweden 0771-400135 (Mobilsamtal – 0,99 kr/min, Lokala samtal – 0,30 kr/min, Utlandssamtal – 0,89 kr/min) Switzerland 022 592 7923

Turkey (0212) 3360303 United Kingdom 0871 222 6702

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners. Product information is subject to change without prior notice.

**EPSON**<sup>®</sup>