

Epson TM-m30II-SL (512): USB + Ethernet + NES + Lightning + SD, Black, PS, EU

DATASHEET / BROCHURE



The TM-m30II-SL is an all-in-one POS solution that's comprised of the TM-m30II and a tablet stand in one stylish, space-saving unit.

This integrated POS solution is compact, easy to use and cost-effective. Users are able to connect a range of tablets (not sold by Epson) to create an all-in-one POS solution that features enhanced connectivity options and design elements.

Advanced connectivity

Peripherals such as scanners, keypads and scales, can connect directly with the TM-m30II-SL and pass data directly to the tablet device. It also includes enhanced connectivity (USB and Ethernet) and Server Direct Print (SDP) and Cloud (OMS) intelligent functionality. It can also accommodate Epson's DM-D70 colour customer display. 'Sync and Charge' provides power and data over a single cable to Android¹ or iOS devices.

Compact and stylish

Features a low profile design and a sliding clamp that means virtually all tablet devices can be securely fixed in place. It can also be installed horizontally or vertically to allow more efficient space management... there's even a wall-hanging option.

Easy to use and reliable

Epson's POS expertise has resulted in unrivalled build quality and refined functionality as each component has been developed with ease of use in mind.

KEY FEATURES

- **All-in-one POS solution**
Printer and tablet stand
- **Discreet design**
Stylish, practical design with small footprint and clean lines
- **Flexibility**
Virtually all tablet devices to be securely fixed in place
- **Enhanced connectivity**
A rich set of connectivity features and options
- **Reliability**
Epson's tried and trusted build quality

PRODUCT SPECIFICATIONS

Print speed	250 mm/sec
PAPER	
Paper size	57.50 ± 0.50 (W) mm x dia 18.00 mm, 57.50 ± 0.50 (W) mm x dia 83.00 mm, 79.50 ± 0.50 (W) mm x dia 18.00 mm, 79.50 ± 0.50 (W) mm x dia 83.00 mm
FONTS & STYLES	
Print Speed receipt	250 mm/sec
Printing Font	ANK
Printing Font Receipt	ANK
Character set	95 Alphanumeric, 18 set International, 128 x 43 Graphic
Dot density	203 DPI x 203 DPI
Printing Characters	Text (incl. Euro symbol), Graphics, Barcode
INTERFACES	
Interfaces	Ethernet interface (100 Base-TX / 10 Base-T), USB 2.0 Type B, USB 2.0 Type A (3x), Drawer kick-out, Micro SD Card Slot
Tablet Charge & Sync	1x
POWER	
Power Supply	PS-180, EURO AC cable
GENERAL	
Product dimensions	140 x 214 x 255 mm (Width x Depth x Height)
Product weight	2.9 kg
Colour	White
Noise Level	Operation (Roll): 55 dB (A)
Installation	vertically
DATA BUFFER	
Data Buffer	12 kB
OTHER	
Warranty	24 months Carry in Optional warranty extension available

LOGISTICS INFORMATION

SKU	C31CH63512
EAN code	8715946696621
Country of Origin	Philippines

Epson TM-m30II-SL (512): USB + Ethernet + NES + Lightning + SD, Black, PS, EU

WHAT'S IN THE BOX

- AC cable
- Roll paper
- Main unit
- Paper spacer
- Power switch cover
- Setup guide
- Warranty document
- Cable fixation saddle
- PS-180

OPTIONAL ACCESSORIES

- OT-BZ20-634: Optional External Buzzer C32C890634
- Epson OT-WL06-323: Wireless LAN dongle 2.4/5GHz WE/CE C32C891323
- Wall hanging unit for TM-m30II-SL C32C881018



For more information please contact:

Home users: 0343 90 37766
Business users*: 0871 42 37766
Republic of Ireland: 01 436 7742
Or visit us at <https://www.epson.co.uk/contactus>
* 10p per minute plus network extras.

Web: www.epson.co.uk
www.epson.ie

1. Data connection requires Android 10 or higher.

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners. Product information is subject to change without prior notice.

EPSON[®]