Epson TM-m50 (131): USB + Ethernet + NES + Serial, White, PS, EU

DATASHEET / BROCHURE











The TM-m50 has been developed for retailers looking for a stylish and compact receipt printer that will fit in with their current POS system.

The TM-m50 provides similar capabilities to a traditional 'legacy' POS printer including a serial connection port, USB-A connection and 180dpi. High volume POS customers will benefit from fast print speeds of up to 350mm/s, and be confident that the printer is supported by Epson's proven quality and reliability.

Compact cube design

The cube design, available in white or black, means it will complement the aesthetics of any modern retail store, and the small footprint means it can fit easily on the counter-top or underneath on the shelf edge. Users of the TM-m50 will also benefit from easy paper loading and advanced paper saving options.

Reliable and easy to use

Epson is the market leader in POS printing¹ with a heritage of producing high-quality and reliable systems. The TM-m50 is a highly intuitive out-of-the-box solution that features: fast print speeds of up to 350mm/s, enhanced printhead and auto-cutter, and flexible drop-in paper loading (front or top).

Legacy print features

The TM-m50 is a feature packed, high performance solution with the legacy features required to allow customers seamless integration into their current systems.

Enhanced connectivity

Flexible connectivity options include serial port and USB-A.

KEY FEATURES

Cube design

Stylish and discreet form to complement retail environments

Legacy fit

Seamless integration into existing systems

Easy to use

A highly intuitive out-of-the-box solution

Connectivity

Serial port and USB-A

Speed

Up to 350mm/s



PRODUCT SPECIFICATIONS

Print speed	350 mm/sec
PAPER	
Paper size	57.50 ± 0.50 (W) mm x dia 18.00 mm,
	57.50 ± 0.50 (W) mm x dia 83.00 mm,
	79.50 ± 0.50 (W) mm x dia 18.00 mm,
	79.50 ± 0.50 (W) mm x dia 83.00 mm
FONTS & STYLES	
Print Speed receipt	350 mm/sec
Print Speed	350 mm/sec
Printing Font	ANK
Printing Font Receipt	ANK
Character set	95 Alphanumeric, 18 set International, 128 x 43 Graphic
Dot density	180 DPI x 180 DPI
Printing Characters	Text (incl. Euro symbol), Graphics, Barcode
INTERFACES	
Interfaces	Ethernet interface (100 Base-TX / 10 Base-T), USB 2.0 Type B, USB 2.0 Type A, Drawer kick-
	out, RS-232C
Tablet Charge & Sync	No
POWER	
Power Supply	PS-180, EURO AC cable
GENERAL	
Product dimensions	127 x 127 x 127 mm (Width x Depth x Height)
Product weight	1.3 kg
Colour	White
Noise Level	Operation: 55 dB (A)
DATA BUFFER	
Data Buffer	12 kB
OTHER	
Warranty	24 months Carry in
	Optional warranty extension available

Epson TM-m50 (131): USB +
Ethernet + NES + Serial, White, PS,

WHAT'S IN THE BOX

- AC cable
- Roll paper
- Main unit
- Paper spacer
- Power switch cover
- Setup guide
- Warranty document
- Cable fixation saddle
- PS-180

OPTIONAL ACCESSORIES

- Wall Hanging Bracket C32C881017
- OT-BZ20-634: Optional External Buzzer C32C890634
- Tablet Stand, Black 7110080

LOGISTICS INFORMATION

SKU	C31CH94131
EAN code	8715946685434
Dimensions Single Carton	490 x 400 x 255 mm
Carton Weight	0 Kg
Country of Origin	China

For more information please contact:

Home users: 0343 90 37766 Business users*: 0871 42 37766 Republic of Ireland: 01 436 7742 Or visit us at https://www.epson.co.uk/contactus * 10p per minute plus network extras. Web: www.epson.co.uk www.epson.ie 1. 1.Number one POS printer manufacturer based on shipments for FY18 (IDC 2019)

