CW-C4000e (mk)



High-quality desktop colour label printer with matte black ink to produce labels in-house and on-demand in small-to-mid volumes

This high-quality desktop printer series has a compact footprint, making it ideal for desktop installations. The C4000 series has a range of easy-to-use features and enhanced connectivity, allowing for increased printing flexibility.

High print quality

The C4000 is a label printer with four colour print output, which prints in high quality, regardless of the label size and material. These label printers offer high-quality, high-resolution, four-colour print output as standard; along with colour matching functionality (ICC profile and spot colour matching tool) for impressive, impactful, on-demand colour labels.

Easy to use

The C4000 is a highly intuitive label printer, straight out of the box. A large (2.7 inches) LCD display panel makes for simple operation. Media rolls can be easily swapped and changed. The model also features an autocutter, which can be easily replaced without the need for an engineer visit.

Simple integration & connectivity

The C4000 range is easy to integrate and connect into existing systems. Drivers are available for ESC Label, Linux and Mac. Our new SDK's for IOS & Android allow easy and intuitive Tablet printing, also adding the optional Wi-Fi dongle gives you the capability to print from anywhere at anytime

Matte black ink

Create crisp, sharp black text and images on matte label media and rich images on plain media.

Durable inks

Thanks to the individual pigment ink cartridges, you can create fast-drying, highly detailed labels that are smudge, water and fade resistant.

KEY FEATURES

- High print quality
 Colour matching functionality and wide colour gamut
- Easy to use Simple setup and highly intuitive
- Integration options
 Fits seamlessly into existing systems
- Peace of mind Comprehensive CoverPlus options
- Matte black ink
 Create crisp, sharp black text and images on matte media



PRODUCT SPECIFICATIONS

TECHNOLOGY

Printing Method PrecisionCore™ Print Head

Category Desktop colour label printer

PRINT

Printing Speed Max. 100 mm/sec at 300 x 600 DPI (printing width 102 mm)

Printing Resolution 1,200 x 1,200 DPI, 1,200 x 600 DPI, 600 x 600 DPI, 300 x 600 DPI, Max. 1,200 x 1,200 DPI

Printing Width max. 108 mm

Print Language ESC/Label, ZPL II (emulation)

SUPPORTED MEDIA

Formats Roll (4" external diameter), Fanfold paper

Type Continuous label, Continuous media, Die-cut label, Black mark paper, Black mark label

GENERAL

Autocutter Yes Included Power Supply AC adapter, C1

Power consumption Printing: Appx. 28 W, Standby: Appx. 3 W

Temperature / humidity Printing: 5~ 35 °C (20~ 80 % RH)

Product dimensions 310 x 285 x 283 mm (Width x Depth x Height)

Sound Power Standby: 58 B (A)

INTERFACES

Tablet Charge No

LOGISTICS INFORMATION

SKU	C31CK03102MK	
EAN code	8715946706559	
Country of Origin	China	

CW-C4000e (mk)

WHAT'S IN THE BOX

- AC adapter
- AC cable
- USB cable
- Label paper roll
- Maintenance box
- Individual Ink Cartridges
- Paper tray

SUPPLIES

- SJIC42P-C (C13T52M240)
- SJIC42P-M (C13T52M340)
- SJIC42P-MK (C13T52M540)
- SJIC42P-Y (C13T52M440)
- High Gloss Label Coil: 220mm x 750m (C33S045529)
- High Gloss Label Continuous Roll: 102mm x 33m (C33S045538)
- High Gloss Label Continuous Roll: 51mm x 33m (C33S045536)
- High Gloss Label Continuous Roll: 76mm x 33m (C33S045537)
- High Gloss Label Die-cut Roll: 102mm x 152mm, 210 labels (C33S045541)
- High Gloss Label Die-cut Roll: 102mm x 51mm, 610 labels (C33S045539)
 High Gloss Label - Die-cut Roll: 102mm x 76mm,
- 415 labels (C33S045540)

 High Gloss Label Die-cut Roll: 76mm x 127mm,
- 250 labels (C33S045543)

 High Gloss Label Die-cut Roll: 76mm x 51mm, 610
- labels (C33S045542)

 PE Matte Label Die-cut Roll: 102mm x 152mm,
- 185 labels (C33S045549)

 PE Matte Label Die-cut Roll: 102mm x 51mm, 535
- labels (C33S045547)

 PE Matte Label Die-cut Roll: 102mm x 76mm, 365
- labels (C33S045548)

 PE Matte Label Die-cut Roll: 76mm x 127mm, 220 labels (C33S045551)
- PE Matte Label Die-cut Roll: 76mm x 51mm, 535 labels (C33S045550)
- PP Matte Label Coil 220mm x 1000lm (C33S045745)
- PP Matte Label Continuous Roll: 102mm x 29m (C33S045744)
- PP Matte Label Continuous Roll: 51mm x 29m (C33S045742)
- PP Matte Label Continuous Roll: 76mm x 29m (C33S045743)
- Premium Matte Label Coil: 220mm x 750m (C33S045528)
- Premium Matte Label Continuous Roll: 102mm x 35m (C33S045419)
- Premium Matte Label Continuous Roll: 105mm x 35m (C33S045727)
- Premium Matte Label Continuous Roll: 51mm x 35m (C33S045417)



Home users: 0343 90 37766 Business users*: 0871 42 37766 Republic of Ireland: 01 436 7742 Or visit us at https://www.epson.co.uk/contactus * 10p per minute plus network extras. Web: www.epson.co.uk www.epson.ie

