

ColorWorks CW-C6500Pe (mk)



This 8-inch colour label printer (with built-in peeler) offers bespoke, flexible, colour labelling and supports a wide range of label sizes.

This on-demand, digital, four-colour label printer opens up new opportunities for businesses with lots of SKUs to manage and not much time. The ColorWorks CW-C6500Pe extends Epson's range in order to meet the needs of small to medium batch customers across many sectors (food, chemical, beverage, manufacturing etc.). This peeler-equipped inkjet label printer is also able to print and peel labels one-by-one.

Media Flexibility

The CW-C6500Pe benefits from a wealth of new features that are designed to provide practical and creative solutions. It supports media widths, from 25.4mm to 215.9mm and boasts expanded media support which even includes textured paper. In practical terms, this range of ColorWorks label printers can print anything from tiny labels for vaping liquid bottles, to large durable labels that are suitable for chemical drums. This matte black ink version of the CW-C6500Pe provides users with increased print finish flexibility on textured or plain paper.

Compact and easy to use

The CW-C6500Pe has been designed to be extremely user friendly. All operations can be carried out from the front, which saves on operation space. The roll replacement is possible from the front, right and left. We've also designed a number of technical tools to help with printer management, configuration and maintenance, including: web interface and printer fleet management, remote configuration, maintenance and monitoring.

Print quality

This label printer offers high quality, high resolution, four-colour print output as standard; along with colour matching functionality (ICC profile and spot colour matching tool) for impressive, impactful, on-demand colour labels.

Easy integration

All models in the range are integration-friendly. SAP direct support, ESC Label, Linux and Mac drivers. Also, the CW-6500Pe (with built-in peeler) can be integrated seamlessly into existing 'print and apply' production lines.

KEY FEATURES

- Media Flexibility**
 Expanded media support. Label widths from 25.4mm to 215.9mm
- Compact**
 Simple, unobtrusive design with front panel operation
- Built-in peeler**
 For print-and-apply production line goods
- Matte black ink version**
 Increased print finish flexibility on textured or plain paper.
- Money saving**
 No need for pre-printed stock of labels. Print full colour on blank labels

PRODUCT SPECIFICATIONS

TECHNOLOGY

Printing Method	PrecisionCore™ Print Head
Nozzle Configuration	800 Nozzles per colour
Category	Industrial colour label printer

PRINT

Printing Speed	Max. 85 mm/sec at 300 x 600 DPI (printing width 212 mm)
Printing Resolution	300 x 600 DPI, 600 x 600 DPI, 600 x 1,200 DPI, 1,200 x 1,200 DPI, Max. 1,200 x 1,200 DPI
Printing Width	max. 212 mm

SUPPORTED MEDIA

Formats	Roll (4" external diameter), Roll (6" external diameter)
Width	Min 25 mm, Max 216 mm
Type	Continuous label, Die-cut label, Black mark label

GENERAL

Power Supply	Internal
Supply voltage	100 ~ 240 V, 50 ~ 60 Hz
Product dimensions	444 x 515 x 326 mm (Width x Depth x Height)
Product weight	26 kg

OTHER

Warranty	12 months On-site service Optional warranty extension available
----------	--

LOGISTICS INFORMATION

SKU	C31CH77202MK
EAN code	8715946691862
Country of Origin	China

ColorWorks CW-C6500Pe (mk)

WHAT'S IN THE BOX

- Driver and utilities (CD)
- User manual
- Individual Ink Cartridges
- Main unit
- Roll paper
- Maintenance box

SUPPLIES

- SJIC36P(M): Ink cartridge for ColorWorks C6500/C6000 (Magenta) (C13T44C340)
- SJIC36P(C): Ink cartridge for ColorWorks C6500/C6000 (Cyan) (C13T44C240)
- SJIC36P(Y): Ink cartridge for ColorWorks C6500/C6000 (Yellow) (C13T44C440)
- SJMB6000/6500: Maintenance box for ColorWorks C6500/C6000 Series (C33S021501)
- High Gloss Label - Die-Cut Roll: 210mm x 297mm, 194 labels (C33S045728)
- Premium Matte Label - Die-Cut Roll: 105mm x 210mm, 282 labels (C33S045740)
- Premium Matte Label - Die Cut Roll: 210mm x 297mm, 200 labels (C33S045738)
- High Gloss Label - Die-Cut: 105mm x 210mm, 273 labels (C33S045730)
- PE Matte Label - Die-Cut Roll: 210mm x 297mm, 184 labels (C33S045732)
- PE Matte Label - Die-Cut Roll: 105mm x 210mm, 259 labels (C33S045734)
- SJIC36P(MK): Ink cartridge for ColorWorks C6500/C6000 (Black) (C13T44C540)

For more information please contact:

Home users: 0343 90 37766
Business users*: 0871 42 37766
Republic of Ireland: 01 436 7742
Or visit us at <https://www.epson.co.uk/contactus>
* 10p per minute plus network extras.

Web: www.epson.co.uk
www.epson.ie

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners.
Product information is subject to change without prior notice.

EPSON®