

Datasheet

Art.No. F0.000.0037.5

antenna WIENET ANTENNE 15874V2 WIFI DACH ANT.

"wienet Omni-roof antenna v2 - 4dBi External antenna WLAN / WiFi Frequency range: 2.4GHz (WLAN) Profit: max. 4dBi connector: 1x SMA / R Cable length: 5m Dimensions: 82x48x48mm incl. Bracket (pole and wall mounting)"



Art.No.	F0.000.0037.5
EAN	4049088328138
Order unit	1 pieces

Approvals

Technical data

Classification

ECLASS 8.1	19070105: Wireless Antenna
ETIM 5.0	EC001698: Wireless Antenna