



BN 22050

Cable Entry Systems

without grommets

Polyamide PA 6 V-0

- Frame: polyamide PA 6 V-0
- Sealing: TPE
- Technology: Tool-free entry and connecting technology for machines and equipment
- Application: Insertion and sealing of pre-assembled cables with connectors into housings
- Variants of grommets: Order as accessory from series F311-9xxx-zz / BN 22051 7 small grommets for cables ØC = 3,0 - 16,5 mm 9 large grommets for cables ØC = 15,0 - 32,5 mm 1 small and 1 large grommet closed
- Mounting: Mounting in wall thicknesses from 1,5 to 2,0 mm, for walls with thicknesses larger than 2,0 mm the KADL can be fixed with screws
- Temperature range: -30 °C / +100 °C
- Protection grade: IP65



Testing standard: UL / CSA-File E140310

Article#	L	L ₁	L ₂	L ₃	S ₂	S ₃	Grommet small / pcs	Grommet large / pcs	h	h ₁	Type	Code
3818998	125	153	35	63	140	50	5	0	32,3	8,9	KADL 5K	F310-9035-02
3818999			57,5	85,5	140	72,5	10	0	32,3	8,9	KADL 10K	F310-9057-01
3819003			80	108	140	95	15	0	32,3	8,9	KADL 15K	F310-9080-03
3819005			102,5	130,5	140	117,5	20	0	32,3	8,9	KADL 20K	F310-9102-02
3819010			125	153	140	140	25	0	32,3	8,9	KADL 25K	F310-9125-04
3818997			35	63	140	50	1	2	32,3	8,9	KADL 1K/2G	F310-9035-01
3819000			80	108	140	95	2	4	32,3	8,9	KADL 2K/4G	F310-9080-01
3819002							6	2	32,3	8,9	KADL 6K/2G	F310-9080-02
3819004			102,5	130,5	140	117,5	11	2	32,3	8,9	KADL 11K/2G	F310-9102-01
3819006			125	153	140	140	3	6	32,3	8,9	KADL 3K/6G	F310-9125-01
3819008							7	4	32,3	8,9	KADL 7K/4G	F310-9125-02
3819009							16	2	32,3	8,9	KADL 16K/2G	F310-9125-03