

Category 5e Keystone Panel Mount Coupler



Category 5e Unshielded Keystone Panel Mount Coupler (FACK2 & FACK2bk-24)

Features

- High performance data throughput, meets Category 5e data transfer rates
- Designed to fit industry standard keystone outlets and patch panels
- Shielded version available (FACK2S)
- Compatible with our 16 and 24 port keystone patch panels available with or without cable management

Packaging

• Supplied in individual polythene bags, then in bags of 20. To save time for panel assemblers, FACK2bk-24 is available as a "bulk pack" of 24 pieces without individual bags

Specifications

Dimensions **FACK2**: 29.5 x 16.9 x 21.8mm (LxWxH) **FACK2bk-24**: 280 x 70 x 35mm (LxWxH)


Weights FACK2: 6 grams
FACK2bk-24: 138 grams

Housing: ABS UL94V-0

Contacts: 50μ"/ 1.27μm gold plating over nickel plated phosphor bronze

Colour: Black (FACK2Bk) and white (FACK2Wh)





TUK Ltd, Unit 4, Wimbledon Stadium Business Centre, Riverside Road, London, SW17 0BA

Tel: 020 8946 6688 Fax: 020 8879 7410 Email: sales@tuk.co.uk Website: www.tuk.co.uk



Category 5e Shielded Keystone Panel Mount Coupler



Category 5e Shielded Keystone Panel Mount Coupler (FACK2S)

Features

- Designed to fit industry standard keystone outlets, wall plates and patch panels
- High performance data throughput, meets Category 5e data transfer rates
- Unshielded versions available
- Plug insertion life ≥ 750 times
- Operating temperature: -40°C ~ +66°C
- Available as part of our innovative Panel Mount and D UNIVERSAL ranges

Packaging:

• Standard product is supplied in individual polythene bags then in bags of 20. To save time for panel assemblers, FACK2S-24 is available as a "bulk-pack" of 24 pieces without individual bags.

Specifications

Materials

Housing: Nickel plated zinc alloy

Contacts: Phosphor bronze, 50µ"/1.27µm gold plated over contact area

Earthing lug material: Stainless steel SUS304

Colour: Silver

Dimensions:


FACK2S: 29.7 x 17 x 22.13 mm (LxWxH) **FACK2S-24**: 280 x 70 x 35 mm (LxWxH)


Weight:


FACK2S: 17g FACK2S-24: 420g approx.





ROHS Compliant Code: FACK2S














ELECTRICAL

CURRENT RATING: 1.5A

DIELECTRIC WITHSTANDING VOLTAGE: 1000VDC

INSULATION RESISTANCE : 500 M Ω MIN. CONTACT RESISTANCE : 20 m Ω MAX.

MECHANICAL

(1) Earthing lug material: Stainless steel SUS304

(2) Front cover: Nickel plated zinc alloy

(3) LATCH: PC FR

(4) Bottom cover: Nickel plated zinc alloy