

RIGHT ANGLE MULTI POSITION (RAMP) METAL XLR PLUGS

Right angle multi position (RAMP) metal XLR plugs are available as either male 3, 4 or 5 pole or female 3 and 5 pole versions. The body is adjustable in 8 positions around the plug to allow cable access to be from any direction. They are supplied with a black strain relief but this can be replaced with a coloured version. There are 9 colours available which are sold separately.





P/Nos.


FC619303 - RAMP 3P XLR MALE PLUG FC619304 - RAMP 4P XLR MALE PLUG FC619305 - RAMP 5P XLR MALE PLUG





FC619313 - RAMP 3P XLR FEMALE PLUG FC619315 - RAMP 5P XLR FEMALE PLUG













Electrical Performance

Contact Resistance: ≤3mΩ Insulation Resistance: >10GΩ Dielectric Strength: 1.5kVdc Rated Voltage: <50V

3 Pin 4Pin 5 Pin Rated Current Per Pin: 15A 10A



Insertion Force: ≤30N Withdrawal Force: ≤30N

≥1000 mating cycles Lifetime: Cable OD range: Ø3.5 to Ø8mm



© CLIFF 02/2023 ISS.1

For further information, contact sales@cliffuk.co.uk

Cliff Electronic Components Limited,

76 Holmethorpe Avenue, Holmethorpe Ind. Estate, Redhill, Surrey RH1 2PF U.K.

Tel: +44 (0)1737 771375 Fax: +44 (0)1737 766012





RIGHT ANGLE MULTI POSITION (RAMP) METAL XLR PLUGS





STRAIN RELIEF WITH COLOURED GROMMETS

P/Nos.

FC619200 - 9 COLOUR GROMMET MULTI PACK

FC619203 - WHITE GROMMET

FC619204 - GREY GROMMET

FC619205 - GREEN GROMMET

FC619206 - YELLOW GROMMET

FC619207 - RED GROMMET

FC619208 - BLUE GROMMET

FC619209 - BROWN GROMMET

FC619210 - ORANGE GROMMET

FC619223 - VIOLET GROMMET

