

# MB 10631



Sample image

**Order symbol :** MB 10631

**EAN :** 6418074030764

**Including :**

**Product nr :** 3540631

**El. number :**

**Description :** Ventilation device IP 33

- Finland : 3422626
- Denmark : 8212008517
- Sweden : 2538442

**Remarks :**

MB\_10631

<b>Dimensions :</b>	<b>Height</b>	<b>Width</b>	<b>Depth</b>
mm :	0	0	0
inch :	0	0	0

**Materials :**

Material :

Base colour :

Cover colour :

Gasket material :

**Rating :**

Ingress protection (EN 60529):

Impact Resistance (EN 62262):

Electrical insulation :

Not insulated

Halogen free (DIN/VDE 0472, Part 815):

0

UV resistance :

-

Flammability Rating :

Glow Wire Test (IEC 695-2-1) °C :

C

NEMA Class

**Temperatures :**

Temperature °C (short term) :

Temperature °C (continuous) :

Temperature °F (short term) :

Temperature °F (continuous) :

**Certificates :**