



Sample image

Order symbol : EKIV 23

Product nr : 4712117

Description : Mounting plate, for enclosures:

Remarks : 300x200x170, 300x200x180

Including :

EAN : 6418074032713

El. number :

- Finland : 3424450
- Denmark : 8212014572
- Sweden : 2539350

EKIV_23-64H

| Dimensions : | Height | Width | Depth |
|---------------------|---------------|--------------|--------------|
| mm : | 170 | 270 | 1 |
| inch : | 6.69 | 10.63 | 0.04 |

Materials :

Material :

Base colour :

Cover colour :

Gasket material :

Rating :

Ingress protection (EN 60529):

Impact Resistance (EN 62262):

Electrical insulation :

Not insulated

Halogen free (DIN/VDE 0472, Part 815):

0

UV resistance :

-

Flammability Rating :

Glow Wire Test (IEC 695-2-1) °C :

C

NEMA Class

Temperatures :

Temperature °C (short term) :

Temperature °C (continuous) :

Temperature °F (short term) :

Temperature °F (continuous) :

Certificates :