



Sample image

**Order symbol :** EKIV 43

**Product nr :** 4712119

**Description :** Mounting plate, for enclosures:

**Remarks :** 400x300x170, 400x300x230, 400x300x180

**EAN :** 6418074032737

**El. number :**

- Finland : 3424452
- Denmark : 8212014598
- Sweden : 2539354

**Including :**

EKIV\_23-64H

<b>Dimensions :</b>	<b>Height</b>	<b>Width</b>	<b>Depth</b>
mm :	370	270	1
inch :	14.57	10.63	0.04

**Materials :**

Material :

Base colour :

Cover colour :

Gasket material :

**Rating :**

Ingress protection (EN 60529):

Impact Resistance (EN 62262):

Electrical insulation :

Not insulated

Halogen free (DIN/VDE 0472, Part 815):

0

UV resistance :

-

Flammability Rating :

Glow Wire Test (IEC 695-2-1) °C :

C

NEMA Class

**Temperatures :**

Temperature °C (short term) :

Temperature °C (continuous) :

Temperature °F (short term) :

Temperature °F (continuous) :

**Certificates :**