

EKIV 27



Sample image

Order symbol : EKIV 27

Product nr : 4712127

Description : DIN-35 Mounting rail, for enclosures:

Remarks : 300x200x170-400x300x230, 300x200x180-400x300x180

EAN : 6418074032775

Including :

El. number :

- Finland : 3424466
- Denmark : 8212015102
- Sweden : 2539364

EKIV_17-47

Dimensions :	Height	Width	Depth
mm :	266	35	1
inch :	10.47	1.38	0.04

Materials :

Material :

Base colour :

Cover colour :

Gasket material :

Rating :

Ingress protection (EN 60529):

Impact Resistance (EN 62262):

Electrical insulation : Not insulated

Halogen free (DIN/VDE 0472, Part 815): 0

UV resistance : -

Flammability Rating :

Glow Wire Test (IEC 695-2-1) °C : C

NEMA Class

Temperatures :

Temperature °C (short term) :

Temperature °C (continuous) :

Temperature °F (short term) :

Temperature °F (continuous) :

Certificates :