

EKIV 44



Sample image

Order symbol : EKIV 44

Product nr : 4712289

Description : Mounting plate, for enclosures:

Remarks : 400x400x170

Including :

EAN : 6418074034984

El. number :

- Finland : 3425535
- Denmark : 8212014556
- Sweden : 2539355

EKIV_44

Dimensions :	Height	Width	Depth
mm :	370	370	1
inch :	14.57	14.57	0.04

Materials :

Material :

Base colour :

Cover colour :

Gasket material :

Rating :

Ingress protection (EN 60529):

Impact Resistance (EN 62262):

Electrical insulation :

Not insulated

Halogen free (DIN/VDE 0472, Part 815):

0

UV resistance :

-

Flammability Rating :

Glow Wire Test (IEC 695-2-1) °C :

C

NEMA Class

Temperatures :

Temperature °C (short term) :

Temperature °C (continuous) :

Temperature °F (short term) :

Temperature °F (continuous) :

Certificates :