

# NEO MPI 3232



Sample image

**Order symbol :** NEO MPI 3232

**Product nr :** 4850071

**Description :** Multiperforated plastic mounting plate

**Remarks :**

**EAN :** 6418074314802

**Including :** Plastic mountingplate

**El. number :**

- Finland : 3424425
- Denmark : 8212098161
- Sweden : 2506229

NEO MPI 3232.jpg

<b>Dimensions :</b>	<b>Height</b>	<b>Width</b>	<b>Depth</b>
mm :	275	265	3
inch :	10.83	10.43	0.12

**Materials :**

Material :	ABS
Base colour :	
Cover colour :	
Gasket material :	

**Temperatures :**

Temperature °C (short term) :	
Temperature °C (continuous) :	
Temperature °F (short term) :	
Temperature °F (continuous) :	

**Rating :**

Ingress protection (EN 60529):	
Impact Resistance (EN 62262):	
Electrical insulation :	Not insulated
Halogen free (DIN/VDE 0472, Part 815):	1
UV resistance :	-
Flammability Rating :	
Glow Wire Test (IEC 695-2-1) °C :	C
NEMA Class	

**Certificates :**