

# PW 343009 T



Sample image

**Order symbol :** PW 343009 T

**Product nr :** 4901824

**Description :** PW Inspection Protection window,

**Remarks :** 342 x 295 x 88 mm, DB3 lock, Transparent cover

**EAN :** 6418074309747

**Including :**

**El. number :**

- Finland : 3424430
- Denmark :
- Sweden :

FIBOX PW\_343009\_T.pdf

<b>Dimensions :</b>	<b>Height</b>	<b>Width</b>	<b>Depth</b>
mm :	342	295	88
inch :	12	10	3.3

#### **Materials :**

Material :	Polycarbonate
Base colour :	
Cover colour :	
Gasket material :	

#### **Temperatures :**

Temperature °C (short term) :	-40 ... 120 °C
Temperature °C (continuous) :	-40 ... 80 °C
Temperature °F (short term) :	-40 ... 250 °F
Temperature °F (continuous) :	-40 ... 175 °F

#### **Rating :**

Ingress protection (EN 60529):	IP66;
Impact Resistance (EN 62262):	IK09;
Electrical insulation :	Not insulated
Halogen free (DIN/VDE 0472, Part 815):	1
UV resistance :	UL 508
Flammability Rating :	UL 94 V0
Glow Wire Test (IEC 695-2-1) °C :	960 °CC
NEMA Class	NEMA 4, 4X, 12 and 13

#### **Certificates :**