

Dimensions :	Height	Width	Depth
mm :	160	360	90
inch :	6.3	14.17	3.54

Materials :

Material :	Aluminum
Base colour :	RAL 7001
Cover colour :	RAL 7001
Gasket material :	Polyurethane

Temperatures :

Temperature °C (short term) :	-50 ... 120
Temperature °C (continuous) :	-50 ... 80
Temperature °F (short term) :	-60 ... 285
Temperature °F (continuous) :	-60 ... 175

Accessories :

AM 1636	Mounting plate, for enclosures: (146 x 346 x 1)
MRS 28541	Wall fastening lug (2 pcs), for enclosures: (15 x 50 x 1)
ARH 1636	DIN-35 Mounting rail, for enclosures: (340 x 35 x 1)

Rating :

Ingress protection (EN 60529):	IP66; IP67; IP68;
Impact Resistance (EN 62262):	IK08;
Electrical insulation :	Not insulated
Halogen free (DIN/VDE 0472, Part 815):	1
UV resistance :	-
Flammability Rating :	
Glow Wire Test (IEC 695-2-1) °C :	C
NEMA Class	

Certificates :

SGSFIMKO_ALU