

PMK NEO 20



Sample image

Order symbol: PMK NEO 20

Product nbr: 4850050

Description: Pole mounting kit

Remarks:

Including: Complete set for pole mounting

EAN: 6418074314543

El. number:

- Finland: 3424427
- Denmark: 8212098187
- Sweden: 2506231

Dimensions:	Height	Width	Depth
mm:	300	200	30
inch:	11.81	7.87	1.18

Materials:

Material:	Stainless steel
Base colour:	
Cover colour:	
Gasket material:	

Temperatures:

Temperature °C (short term)::
Temperature °C (continuous):
Temperature °F (short term):
Temperature °F (continuous):

Rating:

Ingress protection (EN 60529):	
Impact Resistance (EN 62262):	
Electrical insulation:	Not insulated
Halogen free (DIN/VDE 0472, Part 815):	1
UV resistance:	-
Flammability Rating:	
Glow Wire Test (IEC 695-2-1) °C:	C
NEMA Class	

Certificates: