## Flexible cable support

HelaDuct flexible cable supports are commonly used in switching cabinets. They are also used in the furniture industry, where cables need to be routed rapidly and attractively.

## **Features and benefits**

- Space-saving wiring system
- Highly flexible, can be installed at angles of 90° and higher
- · Cable clearly open to view
- Rapid mounting with screws or adhesive strip with high-quality foam bonding layer



HelaDuct Flex can be installed at angles above 90°.

MATERIAL	Polypropylene (PP)		
<b>Operating Temperature</b>	-20 °C to +70 °C, (+80 °C, 200 h)		
Adhesive	Synthetic rubber with base of polyethylene foam		
Flammability	UL 94 V0 (excluding adhesive)		



## **HelaDuct Flex Screw Mounting**

TYPE	Nominal Ø	Fixation Method	No. of Wires		Colour	Length (L)	Pack Cont.	Article-No.
HelaDuct Flex10	10	Screw Mounting	6 x 1.50 mm <sup>2</sup>	4 x 2.50 mm <sup>2</sup>	White (WH)	500	100 pcs.	164-11008
HelaDuct Flex20	20	Screw Mounting	22 x 1.50 mm <sup>2</sup>	14 x 2.50 mm <sup>2</sup>	White (WH)	500	70 pcs.	164-21008
HelaDuct Flex30	30	Screw Mounting	50 x 1.50 mm <sup>2</sup>	34 x 2.50 mm <sup>2</sup>	White (WH)	500	40 pcs.	164-31008
HelaDuct Flex40	40	Screw Mounting	81 x 2.50 mm <sup>2</sup>	60 x 2.50 mm <sup>2</sup>	White (WH)	500	24 pcs.	164-41008

All dimensions in mm. Subject to technical changes. Minimum Order Quantity (MOQ) may differ from package content.

## **HelaDuct Flex Screw Mounting with Adhesive**

TYPE	Nominal Ø	Fixation Method	No. of Wires		Colour	Length (L)	Pack Cont.	Article-No.
HelaDuct Flex10SK	10	Screw Mounting and Adhesive	6 x 1.50 mm <sup>2</sup>	4 x 2.50 mm²	White (WH)	500	100 pcs.	164-11108
HelaDuct Flex20SK	20	Screw Mounting and Adhesive	22 x 1.50 mm <sup>2</sup>	14 x 2.50 mm <sup>2</sup>	White (WH)	500	70 pcs.	164-21108
HelaDuct Flex30SK	30	Screw Mounting and Adhesive	50 x 1.50 mm <sup>2</sup>	34 x 2.50 mm <sup>2</sup>	White (WH)	500	40 pcs.	164-31108
HelaDuct Flex40SK	40	Screw Mounting and Adhesive	81 x 2.50 mm <sup>2</sup>	60 x 2.50 mm <sup>2</sup>	White (WH)	500	24 pcs.	164-41108

All dimensions in mm. Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content.

