

i200/i200s AC Current Clamps

Small sized, convenient to use current clamps



The i200 is a single range 200A clamp-on AC Current Clamp with current output via safety shrouded banana plugs. The i200 is compatible with any Fluke multimeter or any other current measurement device, which has banana inputs.

The i200s is a dual range 20A and 200A clamp-on AC Current Clamp with voltage output via a safety insulated BNC connector. A dual banana to BNC adapter is supplied to allow the i200s to be connected to multimeters with banana input.

i200

- Measuring 0.5 to 240A
- The output signal is 1 mA/A
- Safety shrouded banana plugs for usage with DMMs or any other current measuring device which has banana inputs

i200s

- Measuring range 0.1 to 24A and 0.5 to 240A
- The output signal is 100 mV/A in the 20A range and 10 mV/A in the 200A range
- Includes BNC connector making it suitable for use with any oscilloscope, power analyzer or ScopeMeter® test tool having a compatible BNC input connector
- Dual banana to BNC adapter is included for use with DMMs

i200 and i200s

- Maximum current 240A AC
- 40 Hz to 10 kHz frequency response
- Jaw opening 21 mm
- Maximum conductor size \varnothing 20 mm or busbar 20 x 5 mm
- EN61010, CAT III 600V
- One year warranty

Ordering Information

i200 AC Current Clamp
i200s AC Current Clamp

Need Technical Assistance? Call:
Fluke Corporation
P.O. Box 9090, Everett, WA USA 98206

Fluke Europe B.V.
P.O. Box 1186
5602 BD, Eindhoven
The Netherlands

For more information call:
In the U.S.A. (800) 443-5853 or
Fax (425) 356-5116
In Europe/M-East +31 (0)40 2 678 200 or
Fax +31 (0)40 2 678 222
In Canada (905) 890-7600 or
Fax (905) 890-6866
From other countries +1 (425) 356-5500 or
Fax +1 (425) 356-5116
E-mail: fluke-info@fluke.com
Web access: <http://www.fluke.com/nettools>

© Copyright 1998 Fluke Corporation. All rights reserved. Printed in the Netherlands 12/98. C0209 EEN Rev A.

Fluke. Keeping your world up and running.