





Ø28 928 5'4**:1







Illuminated Emergency-Stop FRVKLOO

Description:

Category: Emergency-Stops

Series: SHORTRON Panel cut-out: Ø 22.3 mm mounting depth: 25 mm

Degree of protection: IP65 / IP67

Illumination: Yes

Contact equipment: 2NC

Connection type: Faston terminals 2.8x0.8 mm

Colour: yellow

component colour: front bezel

Colour 2: red

component colour 2: mushroom head

Shape: round

positive opening: acc. to EN60947-5-1, appendix K

operating temperature: -25°C ... 70°C

mechanical life: 50,000

electrical life: 50,000 at rated load

lamp socket: none, with integrated 3 mm LED

storage temperature: -40°C ... 80°C

foolproof: Yes

switching position indicator: Yes

release: twist right or left contact material: AgNi