
KEMET Part Number: FT0H104ZF

(USCFT00H104Z00)



FT, Supercapacitors, Radial Pin, 0.1 F, -20/+80%, 5.5 VDC, Pin Leads, Lead Spacing = 5.08mm



General Information		
Supplier:	KEMET	
Series:	FT	
Description:	Radial Cylindrical Double Layer	
	Capacitor	
RoHS:	Yes	
Miscellaneous:	DischargeValue = 0.14 F	

Specifications		
Capacitance:	0.1 F	
Capacitance Tolerance:	-20/+80%	
Voltage DC:	5.5 VDC	
Temperature Range:	-40/+85C	
Rated Temperature:	85°C	
Resistance:	16000 mOhms (1kHz)	

Dimensions		
D	11.5mm +/-0.5mm	
L	8.5mm MAX	
S	5.08mm +/-0.5mm	
LL Negative	3mm MIN	
LL Positive	2.7mm MIN	
LT1	0.4mm +/-0.1mm	
LT2	1.2mm +/-0.1mm	

Packaging Specifications	
Lead:	Pin Leads
Packaging:	Bulk, Bag

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

