

| 467B.10**Description
Information**

A [mm]	10
B [mm]	22.7
B1 [mm]	20.2
C [mm]	10.4
E [mm]	5.1
E1 [mm]	7.3
E2 [mm]	3.4
L [mm]	158
[g]	49