

## AutoMax™ 200M Micro-Cut Shredder



- Automatic shredding for maximum productivity
- 200-sheet automatic and 10-sheet manual shredding capacities (70gsm)
- Shreds documents into 2x14mm micro-cut particles (DIN Level P-5) – that's over 2000 particles per A4 sheet!
- Shreds the capacity load in approximately 6 minutes
- 32-litre pull-out waste bin that will need emptying less frequently than the crosscut equivalent
- Also shreds credit cards (manual feed) and staples
- 2-year machine warranty and 7-year cutter warranty

Anti-Jam Technology	Auto-Reverse AUTO REVERSE Stops and reverses paper if a jam occurs
Colour	Black
Country Of Origin	CHINA
Cut Type	MicroShred MICRO Superior security shredding for even greater peace of mind
Energy Savings	Sleep Mode SLEEP Switches to standby mode after periods of inactivity
Item Number	4656401
Noise reduction	SilentShred SILENT Minimises disruption in shared work spaces
Short Description	Auto Feed Shredder with Superior Security Micro-Cut capability
UPC Code	043859726660