


Axial kit EAMM-A-R48-87A

Part number: 1133405

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--------------------------|------------------|
| Mounting position | optional |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Storage temperature | -25 °C ... 60 °C |
| Relative air humidity | 0 - 95% |
| Degree of protection | IP40 |
| Ambient temperature | -10 °C ... 60 °C |
| Transmittable torque | 12.5 Nm |
| Product weight | 590 g |
| Interface code, actuator | R48 |
| Interface code, motor in | 87A |
| Note on materials | RoHS-compliant |