


Flow control/silencer GRU-3/4-B

Part number: 9520

FESTO



Data sheet

Feature	Value
Valve function	Sound pressure control function
Selection of additional functions	With silencer
Pneumatic connection, port 1	G3/4
Adjustment component	Slotted head screw
Type of mounting	Screw-in
Standard flow rate 0.6->0 MPa (6->0 bar, 87->0 psi)	0 l/min ... 8000 l/min
Ambient temperature	-10 °C ... 70 °C
Material housing	Aluminium
Mounting position	optional
Symbol	00991451
Operating pressure complete temperature range	0 bar ... 10 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Media temperature	-10 °C ... 70 °C
Product weight	170 g
Material shock absorber insert	PE
Material screwed plug	Die-cast aluminium
Note on materials	RoHS-compliant
Material adjusting screw	PA