

SPR-PVC-AS

IP 68
-25°C ... +90°C ^ +100°C

EN / IEC 61386-23



Passende Verschraubungen
Suitable connectors

		Seite page	
	US-M	08. 2- 4	IP 65
	US-P	08. 5- 7	
	US2-M	08. 8	IP 65
	USDR-M	08.10	IP 65
	USZ-M	08.12	IP 65
	LI-M P	08.18	IP 40
	LIF-M P	08.19	IP 40
	USW-M	08.20-21	IP 65
	USW-P	08.22-23	

Metall-Schutzschlauch
Stahl verzinkt
PVC-Mantel, nicht flammverbreitend

Protective metal conduit
galvanized steel
PVC sheathing, non flame propagating

KONSTRUKTION

wendelgewickelt
S Profil
PVC-Mantel

STRUCTURE

strip-wound
S profile
PVC sheathing

MATERIAL

Schutzschlauch: Kaltband DC 03/04
nach EN 10139, verzinkt, Fe/Zn 3
Andere Werkstoffe:
Aluminium, nichtrostender Stahl,
Messing blank oder vernickelt
Mantel: PVC
Weitere Werkstoffe auf Anfrage

MATERIAL

Conduit: cold strip DC 03/04
acc. to EN 10139, galvanized, Fe/Zn 3
Further materials:
aluminium, stainless steel,
polished or nickel-plated brass
Sheathing: PVC
Please ask for further materials

EIGENSCHAFTEN

- wetterfest
- wasserdicht
- weitgehend seewasser-, säure-, ölbeständig
- silikon- und cadmiumfrei
- sehr flexibel
- zugfest
- querdruckbelastbar
- DIN 49012, Bauform I geprüft
nach DIN EN IEC 61386-23

PROPERTIES

- weatherproof
- watertight
- widely resistant to seawater, acids, oils
- free of silicone and cadmium
- very flexible
- stretch-resistant
- compression-resistant
- DIN 49012, structural shape I, approved
acc. to DIN EN IEC 61386-23

ANWENDUNGSGEBIETE

- Maschinen- und Anlagenbau
- Fahrzeugbau
- Schiffsbau
- Automation
- Elektroanlagen

APPLICATION

- machine and plant constructions
- automotive
- shipbuilding
- automation
- electrical installations



FLEXA No.

FLEXA No

AD
OD



schwarz black

grau grey

ø

mm

stat

dyn

kg/m

m



2010.112.007	2010.111.007	10	7,0 x 10,0	25	65	0,079	50
2010.112.010	2010.111.010	14	10,0 x 14,0	37	95	0,130	50
2010.112.013	2010.111.013	17	13,0 x 17,0	45	115	0,170	50
2010.112.015	2010.111.015	19	15,0 x 19,0	50	120	0,190	50
2010.112.017	2010.111.017	21	17,0 x 21,0	55	140	0,240	50
2010.112.022	2010.111.022	27	22,0 x 27,0	60	150	0,360	50
2010.112.029	2010.111.029	36	29,0 x 36,0	90	225	0,600	25
2010.112.038	2010.111.038	45	38,0 x 45,0	120	300	0,740	25
2010.112.049	2010.111.049	56	49,0 x 56,0	130	325	0,900	25
Verkaufsverpackung 10 m		10 m sales pack					
2011.112.007	2011.111.007	10	7,0 x 10,0	25	65	0,079	10
2011.112.010	2011.111.010	14	10,0 x 14,0	37	95	0,130	10
2011.112.013	2011.111.013	17	13,0 x 17,0	45	115	0,170	10
2011.112.015	2011.111.015	19	15,0 x 19,0	50	120	0,190	10
2011.112.017	2011.111.017	21	17,0 x 21,0	55	140	0,240	10
2011.112.022	2011.111.022	27	22,0 x 27,0	60	150	0,360	10
2011.112.029	2011.111.029	36	29,0 x 36,0	90	225	0,600	10
2011.112.038	2011.111.038	45	38,0 x 45,0	120	300	0,740	10**
2011.112.049	2011.111.049	56	49,0 x 56,0	130	325	0,900	10**

** in Ringen ** in rings