Fluke SureGrip™ accessories

As tough as your meter



Modular test leads and test probes (use test probes with test leads)

TP175, TwistGuard™ Test Probes

- · Converts probe tip length between 4 mm, a CAT III 1000 V, CAT IV 600 V measurement and 19 mm, a CAT II 1000 V measurement
- · Fits standard modular test leads

FTPL-1 SureGrip™ Fused Test **Probes with Leads**

- FTP-1 Fused Test Probes with built-in fuses for added protection
- TL224 Silicone Insulated Test Leads
- CAT III 1000 V, CAT IV 600 V, 10 A

TL221 SureGrip™ Silicone Test Lead **Extension Kit**

- Superior strain relief
- · Includes two adapters to extend leads 1.5 m
- CAT III 1000 V. CAT IV 600 V, 10 A

TL222 SureGrip™ Silicone Insulated **Test Leads**

- · Superior strain relief
- · Recommended for use with AC220, AC280, AC283 test clips
- CAT III 1000 V. CAT IV 600 V, 10 A

TL224 SureGrip™ **Silicone Insulated Test Leads**

- · Superior strain relief
- 1.5 m siliconeinsulated wire resists heat and cold
- CAT III 1000 V, CAT IV 600 V, 10 A

TL27 Heavy Duty Test Lead Set

- DMM test leads (red, black) with safety shrouded, standard diameter banana plugs
- Heavy duty EPDM insulation
- Length 1.5 m
- CAT III 1000 V. 10 A

TL76 All-in-one Test Lead Set

- One pair (red, black) meter long silicone test leads with right angle shrouded banana plug
- Lantern tip (removable) for use with European wall sockets (4 mm Ø)
- Lantern tip can be removed for easy access to terminal blocks (2 mm Ø)
- Removable, insulated IC caps allow probing on closely spaced leads and compliance with GS38
- CAT IV 600 V, CAT III 1000 V, 10 A

FTP-1 SureGrip™ Fused Test Probes

- Built-in fuses for added protection
- 2 mm threaded probe tips include removable 4 mm lantern-style spring contacts
- Removable GS38 insulated caps
- CAT III 1000 V, CAT IV 600 V, 10 A

TP1, TP2, TP4 and TP38 Slim Reach™ **Test Probes**

- Slender probe bodies for probing closely spaced or recessed points
- TP1 has a flat blade
- TP2 has 2 mm diameter tip
- TP4 has 4 mm diameter tip
- TP38 has stainless steel insulated probe to help lessen the risk of arc flash explosion
- CAT II 1000 V, 10 A
- CAT III 1000 V, CAT IV 600 V with protective cap (TP1 and TP2 only)
- CAT III 1000 V, CAT IV 600 V (TP38 only)

TP74 Lantern Tip Test Probe Set

- One pair (red, black)
- Tips include bananastyle spring contacts with nickel-plated brass ends
- CAT III 1000 V, 10 A

TP220-1 SureGrip™ Industrial Test **Probes**

- Sharp, 13 mm (.5 inch) stainless steel tip provides reliable contact
- Flexible finger barrier improves grip
- CAT II 1000 V, 10 A
- CAT III 1000 V, CAT IV 600 V with protective cap

Modular clips (use with test leads. includes one red, one black)

AC220 SureGrip™ Alligator Clips

- Insulated, nickel plated jaws grip objects up to 10 mm (.375 in)
- Blunt tip grabs round screw
- CAT III 1000 V, CAT IV 600 V,

AC280 SureGrip™ Hook Clips

- Profile narrows to 5.5 mm (.22 inch) at tip
- Hook opening 5 mm (.20 inch) at front, 2 mm (.08 inch) at base
- CAT III 1000 V, CAT IV 600 V, 3 A

AC283 SureGrip™ Pincer

- 11.4 cm (4.5 inch) flexible, insulated shaft
- Nickel plated pincers open to 5 mm (.20 in)
- CAT III 1000 V, CAT IV 600 V, 1 A

AC285 SureGrip™ **Alligator Clips**

- Multi-purpose tooth pattern grips anything from fine gauge wire to a 19 mm (.75 in) nut
- Nickel-plated steel jaws
- Accepts standard modular 4 mm test
- CAT III 1000 V, CAT IV 600 V, 10 A

AC285-FTP Alligator Clips and Adapters for FTP-1 or FTPL-1

- Enhanges the usage of your Fluke fused test leads with this large alligator clip set
- Enables the use of AC285 alligator clips with FTP-1 fused probes
- CAT III 1000 V, CAT IV 600 V, 10 A

AC87 Heavy Duty Bus Bar Clip Set

- One pair (red, black) of flat, right angle design for connecting to bus bars
- Adjustable collar provides 2 ranges of jaw openings up to 30 mm
- CAT III 600 V, 5 A







