

Fluke accessory sets and kits

Get an outstanding value with our most popular accessories



TL220-1 Industrial Test Lead Set

- · Starter kit for industrial applications
- Includes 1 pair: AC220, TP220, TL224
- CAT II 1000 V, 10 A (TP220 only)
- CAT III 1000 V, CAT IV 600 V with protective cap



TL223-1 Electrical Test Lead Set

- Starter kit for electrical applications
- TP1 has flat blades for wall sockets
- Includes 1 pair: AC220, TP1, TL224
- CAT II 1000 V, 10 A (TP1 only)
- CAT III 1000 V, CAT IV 600 V with protective cap



TLK-220 EUR SureGrip™ Accessory Kit with Meter Carrying Case

- Plunger style alligator clips
- Large jaw alligator clips
- Sharp test probes
- Right to straight test leads
- Zippered vinyl carry case with moveable divider
- · Holds large DMMs



TLK287 Electronics Master Test Lead Set

The perfect test lead kit for today's electronics test and design.

- Precision electronic probes with multiple spring-loaded sharp tips to maximize contact with SMD test points
- Micro-grabbers and leads to enable fine SMD test
- Modular mini-alligator clips, grabbers, leads, probes, and couplers EN61010 for virtually every electronics need



TLK289 EUR Industrial Master Test Lead Set and Case

Designed for electrical and electronics test in today's industrial environment.

- SureGrip[™] alligator clips, grabbers and hook clips for dependable contact with a variety of test points
- TP175 TwistGuard[™] Test Probes
- Magnetic hanger for suspension of your DMM
- Temperature adapter with type K thermocouple for direct temperature measurement with your DMMs



TLK-225-1 SureGrip™ Master Accessory Kit

- TP175 TwistGuard™ Test Probes
- Plunger style alligator clips
- Plunger style hook clips
- Plunger style pincer clips
- · Large jaw alligator clips
- Right to straight test leads
- Six-pocket storage pouch, keeps the entire set together



T5-Kit-1, Tester Starter Kit

Getting started kit for electricians who already own a Fluke T5 Tester.

- Test probes
- Large jaw alligator clips
- Zippered soft case

Test lead kits selection guide

	113/114/115/116/117	27 IJ/28 IJ/27	77 IV	175/177/179	83V/87V/233	287/289	434/435	8845A/8846A/8808A	120 Series	190 Series	225C	323/324/325	355	365/373	374 FC/375 FC/376 FC/ 381	902 FC	705/707	71X Series	724/725/726	753/754	181/189	T+/T+Pro	T5-600/T5-1000	1503/1507/1577/1587 FC
TLK287	•	•	•	•	•	•	•	•	•	•	•	•	•				•	•	•	•	•			•
TLK289 EUR	116	•	•		•	•		•	•	•	•			•	•	•				•				
TL220-1	•	•	•	•	•	•	•	•	•	•	•	•	•	•			•	•	•	•	•			•
TL223-1	•	•	•	•	•	•		•	•	•	•			•						•				
TL225-1	•	•	•	•	•	•	•	•	•	•	•	•	•				•	•	•	•	•			•
TL238	•	•	•	•	•	•	•	•	•	•	•	•	•				•	•	•	•	•			•
TL80A-1	•	•	•	•	•	•	•	•	•	•	•	•	•				•	•	•	•	•			•
TL81A	•	•	•	•	•	•	•	•	•	•	•	•	•				•	•	•	•	•			•
80K-8, 80K-15, 80K-40	dc only	•	•	•	•	•		•	•	•	•										•			