# Fluke test leads, probes and clips

The best leads for all your measurement needs

## **For electronic applications**



#### **TL80A-1 Basic Electronic Test Lead Set**

- · Six piece set with zippered case • Probes, alligator clips and tip extenders for electronic applications
- CAT II 300 V
- CAT III 1000 V, CAT IV 600 V with protective cap

#### **TL910 Electronic Test Probes with Replacement Tips**

- Small profile pro-٠
- vides accessibility • Comes with five
- sets of replaceable tips
- · Replacement tips: TP912
- ٠ CAT II 1000 V, 3 A

### **TL912 Replacement Tips**

- for TL910 · Replacement tips
- for TL910 · Five sets of gold plated and stainless steel tips

## **TP80 Electronic Test**

#### **Probes**

- Tapered tip ideal for probing electronic components or boards
- Removable guard for IC probing
- CAT III 1000 V, 10 A

#### **TP920 Test Probe Adapter Kit**

- · IC test tip adapters, extended tips, medium alligator clips fit over TL71 and TL75 test lead sets
- IC test tip Adapter, 3 A
- Extended probe tip, 3 A ٠
- Med. alligator clip, 5 A
- Rated 300 V, 5 A

#### **TLK290 Test Probe** Kit

- · Kit includes three flexible socket probes and a large alligator clip
- To be used on three phase sockets. •
- Probes have flexible width test points that fit securely in 4 to 8 mm sockets.
- Test probe set to be used on motor and three phase sockets
- Safe contact e.g. in CEE

## 16 A and CEE 32 A plugs

CAT II 1000 V, 8 A

Accessories

90

## **TLK291 Fused Test**

- **Probe Set** One pair (red, black)
- fused test probes Designed to meet
  - GS38 specs for United Kingdom CAT III 1000V, 0.5A
- Fuse rating: 500
- mA/1000 V/FF/50 kA

## **TL970 Hook and Pincer**

- Kit TL940 Mini-Hook Test Lead Set
- TL950 Mini-Pincer Test Lead Set
- TL960 Micro-Hook Test Lead Set



#### **TL81A Deluxe Electronic Test Lead Kit**

- Includes components of TL80, plus one pair (red, black) each modular 1 meter long silicone test lead, test probe, hookstyle and pinch style clip, alligator clip, IC probe tip adapter and spade lugs
- Quafold soft carrying case

## **TL40 Retractable Probe**

- Assembly Retractable, insulated
- sharp probe tip
- CAT II 600 V, 3 A

## **TL940 Mini-Hook Test Lead Set**

- 1 pair (red, black) of test leads with multi-stacking 4 mm banana plugs and mini-hooks
- Mini-hooks attach to component
- leads up to 1.5 mm
- diameter
- 90 cm long PVC insulated leads • 30 V rms or 60 V DC, 5 A

## **TL950 Mini-Pincer Test Lead Set**

- 1 pair (red, black) of test leads with multi-stacking 4 mm banana plugs and mini-pincers
- Mini-pincers open to 2.3 mm
- 90 cm long PVC insulated leads
- 30 V rms or 60 V DC, 5 A

#### **TL960 Micro-Hook Test Lead Set**

1 pair (red, black) of test leads with multi-stacking 4 mm banana plugs and micro-hooks



- Micro-hooks attach to component leads up to 1 mm
- diameter
- 90 cm long PVC insulated leads 30 V rms or 60 V DC, 15 A
- ٠

#### TL930 Patch Cord Set (60 cm)

 1 pair (red, black) multi-stacking 4 mm banana plug patch cords



- Nickel-plated banana plugs
- 60 cm long PVC insulated leads
- 30 V rms or 60 V DC, 15 A

#### TL932 Patch Cord Set (90 cm)

- 1 pair (red, black) multi-stacking 4 mm banana plug patch cords
  - Nickel-plated banana plugs
- 90 cm long PVC insulated leads
- 30 V rms or 60 V DC, 15 A

## TL935 Patch Cord Kit (60, 90,

#### 120 cm)


- 3 sets (red and black pairs) of multi-stacking 4 mm banana plug patch cords
- plugs
- cm long PVC insu-
- 30 V rms or 60 V DC, 15 A

### TL26A Telecom Test Lead Set

- Five-way multipoint test clips for telecommunications applications
- Flexible silicone insulated leads are heat
  - and cold resistant Rated 30 V, 8 A



• Nickel-plated banana



lated leads

