

G333 Gaming Earphones



Play at your PC or on the go with immersive and portable gaming audio

Fully immerse into the game with audio purpose-built for play. Dual audio drivers, one for highs/mids and one for bass, deliver incredibly detail-rich sound. Choose from multiple vibrant colours. Select between three flexible, soft ear tips. In-line mic and controls give you clear comms and easy control.

WHAT'S IN THE BOX

- G333 Gaming Earphones
- 3 sizes of ear tips (S, M, L)
- Carrying pouch
- User documentation

FEATURES

G333 Gaming Earphones:

Play at your PC or on the go with immersive and portable gaming audio

Dual gaming-grade drivers for detail-rich audio.

Choose between three sizes of flexible, soft silicone tips.

Sturdy aluminium housing is reliable and durable with an attractive finish.

In-line mic and controls give you clear comms and easy media control.

Connect with 3.5 mm aux connector or included USB-C adapter.

PACKAGE SPECIFICATIONS

	Primary pack	Master shipper carton
Part #	981-000924	N/A
Bar code	5099206092723 (EAN-13)	50992060927210 (SCC-14)
Weight gr	144.9	1680
Length cm	12.5	27
Width cm	9.5	20.5
Height/depth cm	5	14.5
Volume	0.59 dm ³	0.01m ³
1 primary pack	1	N/A
1 master shipper carton	10	1
1 pallet EURO	1540	154
1 container 20 ft	38080	3808
1 container 40 ft	79040	7904
1 container 40 ft HQ	88920	8892

WHITE EMEA

Part #: 981-000930
 EAN: 5099206092730
 Bar code: 50992060927319

PURPLE EMEA

Part #: 981-000936
 EAN: 5099206092747
 Bar code: 50992060927418

BLACK EMEA

Part #: 981-000924
 EAN: 5099206092723
 Bar code: 50992060927210

BOLLYWOOD EMEA

Part #: 981-001041
 EAN: 5099206094659
 Bar code: 50992060946518

SYSTEM REQUIREMENTS

3.5 mm aux or USB-C port

TECHNICAL SPECS

Earphones:

2 dynamic drivers: 5.8 mm + 9.2 mm
 Frequency Response : 20 ~ 20 KHz
 Impedance : 24 Ohms ±20%
 Sensitivity: 101.6±3 dB @ 1 kHz SPL

Microphone:

4mm ECM mic, sensitivity -42dB

Physical Specifications:

Earphones and cable weight: 19 grams
 USB-C adapter weight: 6 grams