



Material: NBR
 Hardness: 70±5 Shore A
 Color: Black
 Remark: With metal inserts
 ISO 2768-m



GF 15-5-3.7

RUBBER FEET(NBR) WITH METAL INSERT, CYLINDRICAL OD: 15mm, HEIGHT: 5mm, HOLE: 3.7mm

Product Properties:

Dimensions:

MOQ	100 .
Unit	pcs

Approvals:

Compliance:

Iron and Steel Sanction	Complied
REACH	No SVHC (Latest. 14 June 2023)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable

Other information:

ETIM-Class	EC004230 - Furniture slider
ETIM-Release	8.0
Trademark	NEMIQ
Product Group	Rubber feet
Search Description	SKV2023ERIK
Alternative SKU	GF15-5-3.7

Logistic information:

Barcode	733117614046
Country of origin	CN

Item status	Non Stock Item, can be on stock but is not a regular stock item.
MOQ	100 .
Stock code	GF 15-5-3.7
Taric code	40169300
Unit	pcs