

## **PRODUCT SPECIFICATION**

## Compact Night & Day Headlamp Model: CH33

#### **Revision History**

Revision	Date	Initiator	Reason for Change
1.0	4 <sup>th</sup> Jan 2019		First Release

Prepared By	Approved By	
Wallace Tso	Wallace Tso	
Date: 4 <sup>th</sup> Jan 2019	Date: 4 <sup>th</sup> Jan 2019	


### **GPI International Limited**


7/F, Building 16W, 16 Science Park West Avenue Hong Kong Science Park, New Territories, Hong Kong, Tel: (852) 2484 3333 Fax: (852) 24805912 Email: gpii@goldpeak.com

Website: http://www.gpbatteries.com

# **GP** Batteries

## **Product Specifications**





Model no.: CH33

Product Name : Compact Night & Day Headlamp

Lumen output\* : Cool white LED: 100lm / 30lm (+/- 15%)

Red LED: 0.7lm (+/- 15%)

Beam Distance\* : Max 40m (+/- 15%)

Runtime : Cool white LED: 100lm: 1.5 hours / 30lm: 6.5 hours

Red LED: 18 hours

Battery type : 1 x AA

LED chip : OSRAM LED

IP rate\* : IPX4

Shock proof\* : Impact resistant, 1m

Dimensions : 60 x 40 x 30 mm

Weight : 54.9 g (without batteries), 78 g (with batteries)

Accessories Included : 1 x AA Batteries

Certification : CE, ROHS



Member
Gold Peak Group
Manufacturer reserves the right to alter or amend the design, model and specification without prior notice.